



Halogen PAR

72PAR38/EVP/FL25 120V 12/1

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.

Product data

General Information	
Cap-Base	E26/50X39 [Skirted Medium Screw (PAR Lamps)]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,100 hour(s)
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	25 degree(s)
Luminous Flux	1,350 lm
Luminous Intensity (Nom)	2,000 cd
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100


Operating and Electrical	
Power Consumption	72 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]

Product Data	
Order product name	72PAR38/EVP/FL25 120V 12/1
Full product name	72PAR38/EVP/FL25 120V 12/1
Order code	925706536306
Material Nr. (12NC)	925706536306
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677428938
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677428933

Halogen PAR

Dimensional drawing



Product

72PAR38/EVP/FL25 120V 12/1

