



# PL-C Cluster 4-Pin Base

## PL-C 26W/830/4P/ALTO 10PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


### Product data

General Information	
Cap-Base	G24q-3
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	26.0 W
Lamp Current (Nom)	0.335 A
Controls and Dimming	
Dimmable	Yes

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	29 kWh
Product Data	
Order product name	PL-C 26W/830/4P/ALTO 10PK
Full product name	PL-C 26W/830/4P/ALTO 10PK
Order code	927907383030
Material Nr. (12NC)	927907383030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677240257
Numerator - Packs per outer box	10
EAN/UPC - Case	60046677240259


# PL-C Cluster 4-Pin Base

## Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 26W/830/4P/ALTO 10PK	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

## Photometric data




Spectral Power Distribution Colour - PL-C 26W/830/4P/ALTO 10PK

## Lifetime



Life Expectancy Diagram - PL-C 26W/830/4P/ALTO 10PK



Life Expectancy Diagram - PL-C 26W/830/4P/ALTO 10PK

## PL-C Cluster 4-Pin Base

### Lifetime



Lumen Maintenance Diagram - PL-C 26W/830/4P/ALTO 10PK

