



# TL-D LIFEMAX Super 80

## TL-D 36W/865 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	15000 h
Life to 50% failures preheat (nom.)	20000 h

Light Technical	
Colour code	865 [ CCT of 6,500 K]
Luminous flux (rated) (nom.)	3070 lm
Colour designation	Cool Daylight
Lumen maintenance 2,000 hours (nom.)	96 %
Lumen maintenance 5,000 hours (nom.)	94 %
Correlated colour temperature (nom.)	6500 K
Luminous efficacy (rated) (nom.)	85 lm/W
Color rendering index (nom.)	80

Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp current (nom.)	0.440 A
Voltage (Nom)	103 V

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg

Product Data	
Full product code	871150028563840
Order product name	TL-D 36W/865 1SL/25
EAN/UPC – product	8711500285638
Order code	28563840
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	927982286536
Net weight (piece)	0.140 kg

# TL-D LIFEMAX Super 80



## Dimensional drawing





TL-D 36W/865 CDL G13

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/865 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

## Photometric data



## Lifetime



## TL-D LIFEMAX Super 80

### Lifetime

