



MASTER TL5 High Efficiency Eco

MASTER TL5 HE Eco 25=28W/865 UNP/40

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HE Eco lamp offers excellent lumen maintenance and colour rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A reduction in energy consumption is only achieved with current-controlled gear.
- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G5 [G5]		96 lm/W
Features	na [Not Applicable]	Color rendering index (CRI)	82
Light Technical		Operating and Electrical	
Color Code	865 [CCT of 6500K]	Power Consumption	25.2 W
Luminous Flux	2,700 lm	Lamp Current (Nom)	0.170 A
Color Designation	Cool Daylight		
Correlated Color Temperature (Nom)	6500 K		

MASTER TL5 High Efficiency Eco

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	T5 [16 mm (T5)]
------------	-----------------

Approval and Application


Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	28 kWh

Product Data

Order product name	MASTER TL5 HE Eco 25=28W/865 UNP/40
--------------------	-------------------------------------


Full product name	MASTER TL5 HE Eco 25=28W/865 UNP/40
Full product code	872790090056900
Order code	927990986531
Material Nr. (12NC)	927990986531
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900900569
Numerator - Packs per outer box	40
EAN/UPC - Case	8727900900569

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Eco 25=28W/865 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm



Photometric data



Spectral Power Distribution Colour - MASTER TL5 HE Eco 25=28W/865 UNP/40


MASTER TL5 High Efficiency Eco

Lifetime



Life Expectancy Diagram - MASTER TL5 HE Eco 25=28W/865 UNP/40

Life Expectancy Diagram - MASTER TL5 HE Eco 25=28W/865 UNP/40



Lumen Maintenance Diagram - MASTER TL5 HE Eco 25=28W/865 UNP/40

