



TL-M Rapid Start Super 80

TL-M RS Super 80 20W/840 1SL/25

The TL-M RS (Rapid Start) Super 80 lamp (tube diameter 38 mm) offers more lumens per watt and better color rendering than TL standard colors. The lamp has an external silicon coating and an external ignition strip. It is suitable for situations where low temperatures and high humidity require fast and stable ignition. Rapid Start lamps can be ignited without a starter.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	57 V	57 V
Life to 50% Failures (Nom)	13,000 hour(s)		
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	1,250 lm	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Shape	T12
Correlated Color Temperature (Nom)	4000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	64 lm/W	Mercury (Hg) Content (Nom)	8.0 mg
Color rendering index (CRI)	85	Energy Consumption kWh/1000 h	24 kWh
Operating and Electrical		Product Data	
Power Consumption	19.3 W	Order product name	TL-M RS Super 80 20W/840 1SL/25
Lamp Current (Nom)	0.370 A		

TL-M Rapid Start Super 80

Full product name	TL-M RS Super 80 20W/840 1SL/25
Full product code	871150072405240
Order code	928030008471
Material Nr. (12NC)	928030008471
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500724052
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500724069

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-M RS Super 80 20W/840 1SL/25	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

Photometric data



Spectral Power Distribution Colour - TL-M RS Super 80 20W/840 1SL/25

