



Ceramalux ALTO

SON 100W E39 ED75 CL SL/12

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)

Light Technical	
Chromaticity Coordinate X (Nom)	520
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	85 lm/W
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	18

Operating and Electrical	
Power Consumption	100.4 W
Lamp Current (Nom)	2.1 A
Voltage (Nom)	55 V
Voltage (Nom)	55 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2

Approval and Application	
Mercury (Hg) Content (Max)	22.1 mg

Product Data	
Order product name	SON 100W E39 ED75 CL SL/12
Full product name	SON 100W E39 ED75 CL SL/12
Order code	928601139890
Material Nr. (12NC)	928601139890
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467241
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467246

Ceramalux ALTO

Dimensional drawing

Product	D	C (max)
SON 100W E39 ED75 CL SL/12	75 mm	196 mm

