



LED PAR30 S/L

12PAR30S/EXPERTCOLOR/F40/927/DIM

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


| General Information | | Wattage Equivalent | |
|---------------------------------------|-----------------------------------|-------------------------------|----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] | | 75 W |
| Nominal lifetime | 40,000 hour(s) | Starting Time (Nom) | 0.5 s |
| Switching Cycle | 50,000 | Warm-up time to 60% light | 0.5 s |
| Lighting Technology | LED | Power Factor (Fraction) | 0.9 |
| EU RoHS compliant | Yes | Voltage (Nom) | 120 V |
| Light Technical | | Temperature | |
| Color Code | 927 | T-Case Maximum (Nom) | 90 °C |
| Beam Angle (Nom) | 40 degree(s) | Controls and Dimming | |
| Luminous Flux | 850 lm | Dimmable | Yes |
| Luminous Intensity (Nom) | 1,800 cd | Mechanical and Housing | |
| Color Designation | Warm White (WW) | Bulb Finish | Clear |
| Correlated Color Temperature (Nom) | 2700 K | Bulb Material | Plastic |
| Luminous Efficacy (rated) (Nom) | 70.00 lm/W | Bulb Shape | PAR30S |
| Color Consistency | <6 | Approval and Application | |
| Color rendering index (CRI) | 95 | Suitable For Accent Lighting | Yes |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | Energy Consumption kWh/1000 h | - kWh |
| Operating and Electrical | | Energy Certifications | Energy Star |
| Line Frequency | 60 Hz | Product Data | |
| Input Frequency | 60 Hz | Order product name | 12PAR30S/EXPERTCOLOR/F40/927/DIM |
| Power Consumption | 12 W | | |
| Lamp Current (Nom) | 120 mA | | |

LED PAR30 S/L

| | |
|-------------------------------|----------------------------------|
| Full product name | 12PAR30S/EXPERTCOLOR/F40/927/DIM |
| Order code | 929001340404 |
| Material Nr. (12NC) | 929001340404 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677470913 |


| | |
|---------------------------------|----------------|
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 50046677470918 |

Dimensional drawing




| Product | D | C |
|----------------------------------|---------|----------|
| 12PAR30S/EXPERTCOLOR/F40/927/DIM | 94.8 mm | 116.1 mm |


Photometric data



Spectral Power Distribution Colour - 12PAR30S/EXPERTCOLOR/F40/927/DIM





Accent Lighting Spots - 12PAR30S/EXPERTCOLOR/F40/927/DIM



Light Distribution Diagram - 12PAR30S/EXPERTCOLOR/F40/927/DIM

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 12PAR30S/EXPERTCOLOR/F40/927/DIM

Lumen Maintenance Diagram - 12PAR30S/EXPERTCOLOR/F40/927/DIM

