



PL-C/T

5PL-C/LED/13H/827/IF5/P/2P 20/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data


General Information		Lamp Current (Max)	
Cap-Base	GX23-2 [GX23-2]	Lamp Current (Max)	50 mA
Nominal lifetime	50,000 hour(s)	Lamp Current (Min)	15 mA
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.9
		Voltage (Nom)	120-277 V
		UL Type	Type A - works on ballast
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	150 degree(s)	T-Case Maximum (Nom)	70 °C
Luminous Flux	520 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	104.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	82	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	140 mm
		Bulb Shape	Tube, single-ended
Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Energy Saving Product	Yes
Input Frequency	50 to 60 Hz		
Power Consumption	5 W		

PL-C/T

Approval Marks	UL certificate RoHS compliance
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	5PL-C/LED/13H/827/IF5/P/2P 20/1
Full product name	5PL-C/LED/13H/827/IF5/P/2P 20/1
Order code	929001884504



Material Nr. (12NC)	929001884504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677532307
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677532302

Dimensional drawing




Product	D	D1	A1	A2	A3
5PL-C/LED/13H/827/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm

Photometric data




General uniform lighting - 5PL-C/LED/13H/827/IF5/P/2P 20/1

Light Distribution Diagram - 5PL-C/LED/13H/827/IF5/P/2P 20/1




Spectral Power Distribution Colour - 5PL-C/LED/13H/827/IF5/P/2P 20/1


Lifetime




Lumen Maintenance Diagram - 5PL-C/LED/13H/827/IF5/P/2P 20/1




Life Expectancy Diagram - 5PL-C/LED/13H/827/IF5/P/2P 20/1



Life Expectancy Diagram - 5PL-C/LED/13H/827/IF5/P/2P 20/1



Life Expectancy Diagram - 5PL-C/LED/13H/827/IF5/P/2P 20/1



Lumen Maintenance Diagram - 5PL-C/LED/13H/827/IF5/P/2P 20/1

