



# TrueForce - LED HID HPL

## TForce LED HPL ND 30-21W E27 840

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) and High Pressure Sodium (SON) lamps. These post-top lamps bring the energy efficiency and long lifetime benefits of LED to HID replacement, delivering instant savings for a low initial investment. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing HPL and SON system, thereby enhancing the light quality with LED HID, without having to change the fixtures or sacrifice the light effect.

### Warnings and Safety

- Installation should always be performed by a qualified electrician or installer. Use the installation guide for instructions
- Link to Ballast – igniter compatibility list <https://www.assets.signify.com/is/content/Signify/Assets/philips-lighting/global/HIDLED-EU-compatibility-list-professional.pdf>

### Product data

General Information		Color Designation	
Cap-Base	E27	Color Designation	Cool White (CW)
Nominal lifetime	50,000 hour(s)	Correlated Color Temperature (Nom)	4000 K
Switching Cycle	50,000	Luminous Efficacy (rated) (Nom)	142 lm/W
Lighting Technology	LED	Color Consistency	<6
Flux measurement reference	Sphere	Color rendering index (CRI)	80
CE mark	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %
EU RoHS compliant	Yes	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
		Stroboscopic effect visibility measure (SVM)	1.6
		Photobiological safety according to EN 62471	RG1
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	360 degree(s)		
Luminous Flux	3,000 lm		

## TrueForce - LED HID HPL

Input Frequency	50 to 60 Hz
Power Consumption	21 W
Lamp Current (Nom)	95 mA
Starting Time (Nom)	0.45 s
Warm-up time to 60% light	0.45 s
Power Factor (Fraction)	0.95
Voltage (Nom)	220-240 V
Inrush current at mains	4.03
Max. lamp no. on MCB B type 10A - Mains	58
Max. lamp no. on MCB B type 10A – EM ballast without Comp. Cap.	58
Max. lamp no. on MCB B type 10A – EM ballast with Comp. Cap.	8
Max. lamp no. on MCB B type 16A - Mains	93
Max. lamp no. on MCB B type 16A – EM ballast without Comp. Cap.	93
Max. lamp no. on MCB B type 16A – EM ballast with Comp. Cap.	14
Ballast Compatibility	EM/Mains

### Temperature

Ambient temperature range	-30 to +45 °C
T-Case Maximum (Nom)	55 °C

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	Others


### Approval and Application

Energy Efficiency Class	D
Energy Consumption kWh/1000 h	21 kWh
EPREL Registration Number	403569

### Product Data

Order product name	TForce LED HPL ND 30-21W E27 840
Full product name	TForce LED HPL ND 30-21W E27 840
Full product code	871869963816000
Order code	929002006202
Material Nr. (12NC)	929002006202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699638160
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699638177


## Dimensional drawing




Product	D	C
TForce LED HPL ND 30-21W E27 840	75 mm	178 mm

# TrueForce - LED HID HPL


## Photometric data



Light Distribution Diagram - TForce LED HPL ND 30-21W E27 840




Spectral Power Distribution Colour - TForce LED HPL ND 30-21W E27 840




© 2024 Philips Lighting B.V. All rights reserved. Page 11

General uniform lighting - TForce LED HPL ND 30-21W E27 840

## Lifetime



Life Expectancy Diagram - TForce LED HPL ND 30-21W E27 840



Lumen Maintenance Diagram - TForce LED HPL ND 30-21W E27 840

## TrueForce - LED HID HPL

