



# SmartBright LED Oyster

## CL261 DS Oyster 15.5W 30-40-65K IP54 ANZ

The new Philips tri-colour Splashproof Oyster offers exceptional value. It is perfect for your everyday lighting installations. It comes with a 3 CCT selection switch to provide flexibility to the customer.

### Product data

General Information	
Light source replaceable	No
Lighting Technology	LED
Light Technical	
Luminous Flux	1,400 lm
Correlated Color Temperature (Nom)	3000 4000 6500 K
Luminous Efficacy (rated) (Nom)	87.00 lm/W
Color rendering index (CRI)	80
Light source color	3000/4000/6500
Luminaire light beam spread	110°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	15.5 W
Power Factor (Fraction)	0.9


Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Material	Metal-Plastic
Housing Color	White
Overall length	87 mm
Overall width	87 mm
Overall height	88 mm
Overall diameter	300 mm
Dimensions (Height x Width x Depth)	88 x 87 x 87 mm
Approval and Application	
Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

SmartBright LED Oyster


Over Time Performance (IEC Compliant)	
Median useful life L70B50	30,000 hour(s)
Product Data	
Order product name	CL261 DS Oyster 15.5W 30-40-65K IP54 ANZ
Full product name	CL261 DS Oyster 15.5W 30-40-65K IP54 ANZ
Full product code	871951426677300
Order code	929002562219

Material Nr. (12NC)	929002562219
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514266773
Numerator - Packs per outer box	5
EAN/UPC - Case	8719514266780

Dimensional drawing




Photometric data




General uniform lighting - CL261 DS Oyster 15.5W 30-40-65K IP54 ANZ

SmartBright LED Oyster

Lifetime



Life Expectancy Diagram - CL261 DS Oyster 15.5W 30-40-65K IP54 ANZ



Lumen Maintenance Diagram - CL261 DS Oyster 15.5W 30-40-65K IP54 ANZ

