



01- The product should only be installed indoors.

01- 产品只能安装在室内。

02- The product is not suitable for installation in bathrooms, certainly not in the specified zone.

02- 产品不可安装在浴室中，尤其不能在指定区域内。

03- The product is suitable for mounting on normally flammable surfaces.

03- 产品可安装在普通易燃表面。

04- The product is suitable for mounting on the wall or on the ceiling.

04- 产品可安装在墙上或天花板上。

05- Protection class III: the product or component is only suitable for safety extra low voltage supply (<50V a.c.; <120V d.c.).

05- 防护等级 III：产品或组件仅用于安全超低供电电压（交流<50伏、直流<120伏）。

LED strip do not connect with LED driver during transportation.

灯带在包装盒里不得接通电源。

LED strip can not be electrical connection with unspecified Philips light strip.

本灯带不得与非指定飞利浦灯带电气连接。

LEDs are un-replaceable, only allow to replace identical Philips LED strip.

灯珠不可更换。

30W driver is included, the input voltage is 220-240V~ 50/60Hz.

LED strip power consume: 3.6W/m.

本产品含30W电源驱动器，驱动器输入电压220-240V~ 50/60Hz。

灯带消耗功率：3.6瓦/米。

Decorative LED strip

装饰性LED灯带

PHILIPS

