Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's address: Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

Model identifier:	9290036253
-------------------	------------

Type of light sou

Lighting technology used:	LED	Non-directional or directional:	NDLS	
Light source cap-type	E27			
(or other electric interface)				
Mains or non-mains:	MLS	Connected light source (CLS):	No	
Colour-tuneable light source:	No	Envelope:	-	
High luminance light source:	No			
Anti-glare shield:	No	Dimmable:	No	
Product parameters				

Product parameters

Product parameters					
Parameter		Value	Parameter	Value	
	General product parameters:				
Energy consummode (kWh/10) up to the neares	00 h), rounded	8	Energy efficiency class	А	
dicating if it refe a sphere (360°),	s flux (φuse), in- ers to the flux in , in a wide cone rrow cone (90º)	1 535 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	2 700	
On-mode pow pressed in W	ver (P _{on}), ex-	7,3	Standby power (P _{sb}), expressed in W and rounded to the sec- ond decimal	0,00	
	andby power expressed in W the second dec-	-	Colour rendering in- dex, rounded to the nearest integer, or the range of CRI-val- ues that can be set	80	
Outer dimen-	Height	104	Spectral power dis-	See image	
sions without	Width	60	tribution in the	in last page	
separate con- trol gear, light- ing control	Depth	60	range 250 nm to 800 nm, at full-load		

parts and non- lighting con- trol parts, if any (millime- tre)					
Claim of equivalent power ^(a)	Yes	If yes, equivalent power (W)	100		
		Chromaticity coordi-	0,470		
		nates (x and y)	0,429		
Parameters for LED and OLED I	Parameters for LED and OLED light sources:				
R9 colour rendering index value	9 0	Survival factor	0,90		
the lumen maintenance factor	0,96				
Parameters for LED and OLED mains light sources:					
displacement factor (cos φ1)	0,50	Colour consistency in McAdam ellipses	6		
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.	-	If yes then replace- ment claim (W)	-		
Flicker metric (Pst LM)	1,0	Stroboscopic effect metric (SVM)	0,4		

(a)'-': not applicable; (b)'-': not applicable;

