

Project		Catalog #		Type	
Prepared by		Notes		Date	



Sure-Lites

All-Pro APWR Series

Wet location LED remote head
 Polycarbonate construction
 Up to 17 feet of emergency egress coverage

Typical Applications

Office • Education • Healthcare • Hospitality • Retail • Industrial • Manufacturing

Interactive Menu

- Order Information page 2
- Photometric Data page 2
- Product Warranty

Product Certification



Product Features




wet location



Top Product Features

- LED remote up to 17 feet of coverage
- Wet location listed
- 3.6 V input; single or double head options
- Polycarbonate construction
- -30° C to 55° C operating temperature
- Compatible with Sure-Lites APELH, APCH and APXH7 emergency lighting models

Dimensional Details



additional product diagrams

APWR2BK

SAMPLE ORDER NUMBER: **APWR2BK**


Order Information

Series	Remote Heads	Housing Color	Catalog Numbers
APWR	1=one LED head 2= two LED heads	_ =White BK=Black	APWR1, APWR2, APWR1BK, APWR2BK

Photometric Data

[View IES files](#)

APWR Spacing



Product Specifications

Electrical

- 3.6V DC Input Voltage

Lampholder/Mounting Plate Construction

- Flame resistant and impact resistant, injection molded thermoplastic
- Lamp heads adjust 80° from vertical with 358° rotation
- Universal mounting plate
- Available in white or black

Code Compliance

- UL 924 Listed
- Wet Location Listed
- California Energy Code compliant

Head/Lamp Data

- Long Life LED Emergency Heads
- Fully adjustable
- High impact thermoplastic
- Matches housing finish
- 3.6V, .78W DC Long Lasting LED Heads

Sure-Lites All-Pro Compatible Products

- APELH series emergency light with remote capability
- APCH7 series exit and emergency light combo with remote capability
- APXH7 exit series with remote capability

Warranty

- Limited five-year warranty

Energy and Performance Data

Power Consumption is equal to LED head wattage.