


HL3 3" Round Trim Series


Recessed 3-inch aperture LED downlight / directional with field interchangeable optics provide various distribution patterns. Ideal for accent, task and general area lighting. Housing is airtight, suitable for 2x6 residential or shallow plenum commercial constructions and can be used in direct contact with insulation. Trims are available in a range of finishes and can be installed rimless with an optional rimless adapter. Use where high efficiency, excellent light control and low aperture brightness are required.

| | | |
|-------------|--|------|
| Catalog # | | Type |
| Project | | |
| Comments | | Date |
| Prepared by | | |



DIRECTIONAL OPEN




TL3R
Conical Reflector,
Open, Self Flanged





| Trim | Shielding | Finish | Flange |
|--|-----------------------|--|--|
| TL3R = 3.25" aperture conical reflector, open, self-flanged | [blank] = open | Anodized Finishes H = semi-specular clear reflector and flange HWF = semi-specular clear reflector and matte white flange Electroplated Finishes BN = brushed nickel reflector and flange ORB = oil rubbed bronze reflector and flange Painted Finishes MW = matte white reflector and flange MB = matte black reflector and flange | [blank] = full overlap self-flanged |



TL3RMWRL
Conical Reflector,
Open, Rimless




| Trim | Shielding | Finish | Flange |
|---|-----------------------|---|---|
| TL3R = 3.25" aperture conical reflector, open, rimless | [blank] = open | Painted Finishes MW = matte white reflector and flange | RL = rimless, must be used with rimless adapter ordered separately |





DIRECTIONAL OPEN




TL3BBWF
TL3WBWF
Conical Baffle,
Open, Self Flanged





| Trim | Shielding | Finish | Flange |
|---|----------------|---|-------------------------------------|
| TL3R = 3.25" aperture conical baffle, open, self-flanged | [blank] = open | Painted Finishes BBMF = matte black baffle, matte white flange WBWF = matte white baffle, matte white flange | [blank] = full overlap self-flanged |




TL3PIN
Round Pinhole w/Oculus,
Open, Self Flanged





| Trim | Shielding | Finish | Flange |
|---|----------------|--|-------------------------------------|
| TL3PIN = 2.00" aperture pinhole w/oculus, open, self-flanged | [blank] = open | Electroplated Finishes BNBB = brushed nickel flange, black oculus ORBBB = oil rubbed bronze flange, black oculus Painted Finishes MWWB = matte white flange, white oculus MWBB = matte white flange, black oculus MBBB = matte black flange, black oculus | [blank] = full overlap self-flanged |



TL3PINMWWBRL
Round Pinhole w/Oculus,
Open, Rimless




| Trim | Shielding | Finish | Flange |
|--|----------------|---|---|
| TL3PIN = 2.00" aperture pinhole w/oculus, open, rimless | [blank] = open | Painted Finishes MWWB = matte white flange, white oculus | RL = rimless, must be used with rimless adapter ordered separately |





DIRECTIONAL LENS




TL3R2G
Conical Reflector,
Diffuse Lens, Self Flanged





| Trim | Shielding | Finish | Flange |
|--|----------------------------------|--|--|
| TL3R = 3.25" aperture conical reflector, open, self-flanged | 2G = micro-prismatic lens | Anodized Finishes H = semi-specular clear reflector and flange HWF = semi-specular clear reflector and matte white flange Electroplated Finishes BN = brushed nickel reflector and flange ORB = oil rubbed bronze reflector and flange Painted Finishes MW = matte white reflector and flange MB = matte black reflector and flange | [blank] = full overlap self-flanged |




TL3R2GMWRL
Conical Reflector,
Diffuse Lens, Rimless





| Trim | Shielding | Finish | Flange |
|---|----------------------------------|--|---|
| TL3R = 3.25" aperture conical reflector, open, rimless | 2G = micro-prismatic lens | Painted Finishes MW = matte white reflector and flange | RL = rimless, must be used with rimless adapter ordered separately |



TL3PR2GMW
Conical Polymer Reflector,
Diffuse Lens, Self Flanged




| Trim | Shielding | Finish | Flange |
|--|----------------------------------|--|--|
| TL3R = 3.25" aperture conical polymer reflector, lens, self-flanged | 2G = micro-prismatic lens | Painted Finishes MW = matte white reflector and flange | [blank] = full overlap self-flanged |





DIRECTIONAL LENS




TL3R2GBBWF
TL3R2GWBWF
Conical Baffle,
Diffuse Lens, Self Flanged





| Trim | Shielding | Finish | Flange |
|---|----------------------------------|---|--|
| TL3R = 3.25" aperture conical baffle, open, self-flanged | 2G = micro-prismatic lens | Painted Finishes BBMF = matte black baffle, matte white flange WBWF = matte white baffle, matte white flange | [blank] = full overlap self-flanged |




TL3PIN2G
Round Pinhole w/Oculus,
Diffuse Lens, Self Flanged





| Trim | Shielding | Finish | Flange |
|---|----------------------------------|--|--|
| TL3PIN = 2.00" aperture pinhole w/oculus, open, self-flanged | 2G = micro-prismatic lens | Electroplated Finishes BNBB = brushed nickel flange, black oculus ORBBB = oil rubbed bronze flange, black oculus Painted Finishes MWWB = matte white flange, white oculus MWBB = matte white flange, black oculus MBBB = matte black flange, black oculus | [blank] = full overlap self-flanged |




TL3PIN2GMWWBRL
Round Pinhole w/Oculus,
Diffuse Lens, Rimless




| Trim | Shielding | Finish | Flange |
|--|----------------------------------|---|---|
| TL3PIN = 2.00" aperture pinhole w/oculus, open, rimless | 2G = micro-prismatic lens | Painted Finishes MWWB = matte white flange, white oculus | RL = rimless, must be used with rimless adapter ordered separately |






LENS WALL WASH




TL3LWW6G
Conical Angle Cut Lens
Wall Wash, Self Flanged



| Trim | Shielding | Finish | Flange |
|---|--------------------------------|---|--|
| TL3LWW = 3.25" aperture conical lens wall wash, self-flanged | 6G = linear spread lens | Anodized Finishes H = semi-specular clear reflector and flange HWF = semi-specular clear reflector and matte white flange Painted Finishes MW = matte white reflector and flange | [blank] = full overlap self-flanged |



TL3LWW6GMWRL
Conical Angle Cut Lens
Wall Wash, Rimless



| Trim | Shielding | Finish | Flange |
|--|--------------------------------|---|---|
| TL3LWW = 3.25" aperture conical lens wall wash, rimless | 6G = linear spread lens | Painted Finishes MW = matte white reflector and flange | RL = rimless, must be used with rimless adapter ordered separately |

