Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: PHILIPS

Supplier's address: Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

Model identifier: 9290013933B

_	•			
Ivpe	Ot	light	source:	

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type	G13 ROT		
(or other electric interface)			
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No

Product parameters

Product parameters						
Parameter		Value	Parameter	Value		
General product parameters:						
<u> </u>	mption in on- 00 h), rounded st integer	8	Energy efficiency class	E		
dicating if it refe a sphere (360º)	s flux (фuse), ineers to the flux in, in a wide cone arrow cone (90º)	1 050 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	6 500		
On-mode pow pressed in W	ver (P _{on}), ex-	8,0	Standby power (P _{sb}), expressed in W and rounded to the sec- ond decimal	0,00		
(P _{net}) for CLS, 6	tandby power expressed in W the second dec-	-	Colour rendering in- dex, rounded to the nearest integer, or the range of CRI-val- ues that can be set	80		
Outer dimen-	Height	603	Spectral power dis-	See image		
sions without	Width	28	tribution in the	in last page		
separate con- trol gear, light- ing control	Depth	28	range 250 nm to 800 nm, at full-load			

parts and non- lighting con- trol parts, if any (millime- tre)					
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-		
		Chromaticity coordi-	0,312		
		nates (x and y)	0,328		
Parameters for LED and OLED light sources:					
R9 colour rendering index value	0	Survival factor	0,90		
the lumen maintenance factor	0,96				

(a)'-': not applicable; (b)'-': not applicable;

