

without separate control gear, lighting control parts and non-lighting control parts, if any (millimetre)	Depth	51	range 250 nm to 800 nm, at full-load	
Claim of equivalent power ^(a)		Yes	If yes, equivalent power (W)	50
			Chromaticity coordinates (x and y)	0,458 0,410
Parameters for directional light sources:				
Peak luminous intensity (cd)		1 600	Beam angle in degrees, or the range of beam angles that can be set	36
Parameters for LED and OLED light sources:				
R9 colour rendering index value		0	Survival factor	0,90
the lumen maintenance factor		0,96		

(a) '-': not applicable;

(b) '-': not applicable;

