



# Infrared Lamps Industrial Use

## 125BR40 IR/1 120V 4/1 TP


The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

### Product data

General Information		Bulb Material	
Cap-Base	E26 [Single Contact Medium Screw]	Bulb Material	Hard Glass
Nominal lifetime	5,000 hour(s)	Bulb Shape	BR40
Lighting Technology	Incandescent	<b>Product Data</b>	
Operating and Electrical		Order product name	125W BR40 Medium Base Heat Lamp
Power Consumption	125 W	Full product name	125BR40 IR/1 120V 4/1 TP
Wattage Equivalent	125 W	Order code	416750
Voltage (Nom)	120 V	Material Nr. (12NC)	925254936311
Controls and Dimming		Numerator - Quantity Per Pack	1
Dimmable	No	Net Weight (Piece)	0.75 lb
		EAN/UPC - Product/Case	046677416751
Mechanical and Housing		Numerator - Packs per outer box	4
Bulb Finish	Clear	EAN/UPC - Case	50046677416756

# Infrared Lamps Industrial Use

## Dimensional drawing



Product	D	C (max)
125W BR40 Medium Base Heat Lamp	4-15/16 inch	6-7/8 inch

