



InfraRed Industrial Heat Incandescent

250BR40 IR/1 120V 4/1 TP

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

| General Information | |
|------------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Rated Lifetime (Hours) | 5,000 hour(s) |
| Lighting Technology | Incandescent |

| Operating and Electrical | |
|--------------------------|-------|
| Power Consumption | 250 W |
| Voltage (Nom) | 120 V |
| Voltage (Nom) | 120 V |


| Mechanical and Housing | |
|------------------------|-------|
| Bulb Finish | Clear |

| | |
|------------|------|
| Bulb Shape | BR40 |
|------------|------|

| Product Data | |
|---------------------------------|--------------------------|
| Order product name | 250BR40 IR/1 120V 4/1 TP |
| Full product name | 250BR40 IR/1 120V 4/1 TP |
| Order code | 416743 |
| Material Nr. (12NC) | 925255136310 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677416744 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 50046677416749 |

InfraRed Industrial Heat Incandescent

Dimensional drawing



Product

250BR40 IR/1 120V 4/1 TP

