



TL-D LIFEMAX Super 80

18 W G13 Warm white Linear fluorescent tube

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.


Product data

Informasi Umum	
Tutup-Dasar	G13 [Medium Bi-Pin Fluorescent]
Nominal masa pakai	15.000 jam
Masa Pakai hingga 50 % Kegagalan (Nom)	13.000 jam
Teknis Lampu	
Kode Warna	830 [CCT of 3000K]
Penandaan Warna	Warm White (WW)
Daya Penerangan (terukur) (Nom)	75 lm/W
Suhu Warna Terkorelasi (Nom)	3000 K
Indeks renderasi warna (CRI)	83
Pengoperasian dan Kelistrikan	
Konsumsi Daya	18 W
Arus Lampu (Nom)	0,360 A
Tegangan (Nom)	59 V
Kontrol dan Peredupan	
Dapat diredupkan	Ya

Mekanis dan Housing	
Bentuk Bohlam	T8
Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	2,0 mg
Data Produk	
Nama produk pesanan	18 W G13 Warm white Linear fluorescent tube
Nama lengkap produk	18 W G13 Warm white Linear fluorescent tube
Kode produk lengkap	871150028558400
Kode urutan	927980283036
No. Material (12NC)	927980283036
Numerator - Jumlah Per Pak	1
Berat Bersih (Bagian)	0,070 kg
EAN/UPC - Produk/Kantung	8711500285584
Numerator - Pak per kotak bagian luar	25
EAN/UPC - Kantung	8711500285799


TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
18 W G13 Warm white Linear fluorescent tube	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Photometric data




Spectral Power Distribution Colour - TL-D 18W/830 1SL/25

Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

TL-D LIFEMAX Super 80

Lifetime



Lumen Maintenance Diagram - TL-D 18W/830 1SL/25

