



TL-D LIFEMAX Super 80

TL-D 58W/865 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T8 [26 mm (T8)]
Nominal lifetime	15,000 hour(s)		
Life to 50% Failures (Nom)	15,000 hour(s)		
Light Technical		Approval and Application	
Color Code	865 [CCT of 6500K]	Mercury (Hg) Content (Nom)	2.0 mg
Color Designation	Cool Daylight		
Correlated Color Temperature (Nom)	6500 K	Product Data	
Luminous Efficacy (rated) (Nom)	82 lm/W	Order product name	TL-D 58W/865 1SL/25
Color rendering index (CRI)	80	Full product name	TL-D 58W/865 1SL/25
		Full product code	871150028496940
Operating and Electrical		Order code	927983286536
Power Consumption	58.5 W	Material Nr. (12NC)	927983286536
Lamp Current (Nom)	0.670 A	Numerator - Quantity Per Pack	1
Voltage (Nom)	111 V	EAN/UPC - Product/Case	8711500284969
Voltage (Nom)	111 V	Numerator - Packs per outer box	25
		EAN/UPC - Case	8711500284976
Controls and Dimming			
Dimmable	Yes		


TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/865 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - TL-D 58W/865 1SL/25

Lifetime




Life Expectancy Diagram - TL-D 58W/865 1SL/25



Life Expectancy Diagram - TL-D 58W/865 1SL/25

TL-D LIFEMAX Super 80

Lifetime



Lumen Maintenance Diagram - TL-D 58W/865 1SL/25

