



TL-D Standard Colours

18 W G13 Cool daylight Linear fluorescent tube

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Nominal lifetime	13,000 hour(s)		
Life to 50% Failures (Nom)	13,000 hour(s)	Mechanical and Housing	
		Bulb Shape	T8
Light Technical		Approval and Application	
Color Code	54-765	Mercury (Hg) Content (Nom)	8.0 mg
Luminous Flux	1,050 lm	Energy Consumption kWh/1000 h	22 kWh
Color Designation	Cool Daylight		
Correlated Color Temperature (Nom)	6200 K	Product Data	
Color rendering index (CRI)	72	Order product name	18 W G13 Cool daylight Linear fluorescent tube
Operating and Electrical		Full product name	18 W G13 Cool daylight Linear fluorescent tube
Power Consumption	18.0 W	Full product code	871150070267840
Lamp Current (Nom)	0.360 A	Order code	928048005436
Voltage (Nom)	59 V	Material Nr. (12NC)	928048005436
		Numerator - Quantity Per Pack	1
		Net Weight (Piece)	0.070 kg

TL-D Standard Colours


EAN/UPC - Product/Case	8711500702678
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500727145

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
18 W G13 Cool daylight Linear fluorescent tube	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data




Spectral Power Distribution Colour - TL-D 18W/54-765 1SL/25

Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 18W/54-765 1SL/25

