



TL-D Standard Colours

36 W G13 Cool daylight Linear fluorescent tube

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Nominal lifetime	13,000 hour(s)		
Life to 50% Failures (Nom)	13,000 hour(s)	Mechanical and Housing	
		Bulb Shape	T8
Light Technical		Approval and Application	
Color Code	54-765	Mercury (Hg) Content (Nom)	8.0 mg
Luminous Flux	2,500 lm	Energy Consumption kWh/1000 h	43 kWh
Color Designation	Cool Daylight		
Correlated Color Temperature (Nom)	6500 K	Product Data	
Color rendering index (CRI)	72	Order product name	36 W G13 Cool daylight Linear fluorescent tube
Operating and Electrical		Full product name	36 W G13 Cool daylight Linear fluorescent tube
Power Consumption	36.0 W	Full product code	871150070271540
Lamp Current (Nom)	0.440 A	Order code	928048505436
Voltage (Nom)	103 V	Material Nr. (12NC)	928048505436
		Numerator - Quantity Per Pack	1
		Net Weight (Piece)	0.140 kg
		EAN/UPC - Product/Case	8711500702715

TL-D Standard Colours


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500727763

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
36 W G13 Cool daylight Linear fluorescent tube	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - TL-D 36W/54-765 1SL/25

Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 36W/54-765 1SL/25

