



CorePro LEDspot Reflectors

LED 10W E27 6500K 230V R80 AU

CorePro LEDspots Reflectors are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E27 base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots Reflectors deliver significant energy savings and minimize maintenance cost.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	950 lm
Color Designation	Cool Daylight
Luminous Efficacy (rated) (Nom)	95 lm/W
Correlated Color Temperature (Nom)	6500 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0


Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	65 mA
Wattage Equivalent	80 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	72 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic

CorePro LEDspot Reflectors

Bulb Shape	R80
Approval and Application	
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	10 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Product Data	
Order product name	LED 10W E27 6500K 230V R80 AU
Full product name	LED 10W E27 6500K 230V R80 AU



Full product code	871869959375900
Local code description	LED10WR80E27CW
Order code	929001858119
Material Nr. (12NC)	929001858119
Local order code	LED10WR80E27CW
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.036 kg
EAN/UPC - Product/Case	8718699593759
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699650346

Dimensional drawing



Product	D	C
LED 10W E27 6500K 230V R80 AU	80 mm	115 mm

Photometric data




Spectral Power Distribution Colour - LED 10W E27 6500K 230V R80 AU

Light Distribution Diagram - LED 10W E27 6500K 230V R80 AU

CorePro LEDspot Reflectors

Photometric data




CalcLoX Photometrics 4.3 Philips Lighting B.V. Page 1/1

Accent Lighting Spots - LED 10W E27 6500K 230V R80 AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED 10W E27 6500K 230V R80 AU

