



LED BR30

7.2BR30/COR/950/P/E26/DIM 6/1FB T20

Philips BR30 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	110 degree(s)
Luminous Flux	650 lm
Color Designation	Daylight
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Correlated Color Temperature (Nom)	5000 K
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	7.2 W
Lamp Current (Nom)	82 mA


Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	BR30
UL Wet/ damp/ dry location	Damp location
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
EU RoHS compliant	Yes
EyeComfort	Yes

LED BR30

T20 compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	7.2BR30/PER/950/P/E26/DIM 6/1FB T20
Full product name	7.2BR30/COR/950/P/E26/DIM 6/1FB T20
Order code	548107



Material Nr. (12NC)	929002204163
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.121 lb
EAN/UPC - Product/Case	046677548100
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677548105

Dimensional drawing



Product	D	C
7.2BR30/PER/950/P/E26/DIM 6/1FB T20	3-3/4 inch	5-1/4 inch

Photometric data




General uniform lighting - 7.2BR30/COR/950/P/E26/DIM 6/1FB T20

Light Distribution Diagram - 7.2BR30/COR/950/P/E26/DIM 6/1FB T20


LED BR30

Photometric data




Spectral Power Distribution Colour - 7.2BR30/COR/950/P/E26/DIM 6/1FB T20

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 7.2BR30/COR/950/P/E26/DIM 6/1FB T20

