



Essential LEDspot PAR

LED 14-120W PAR38 827 25D

Essential LED PAR is an affordable LED spot lamp that is designed as a retrofit replacement for halogen spots PAR lamps. It provides a natural lighting effect as well as instant energy savings – an environment-friendly solution. The Philips Essential LED family is designed for spot and general lighting applications in the hospitality and retail segments.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED

Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	1,200 lm
Luminous Intensity (Nom)	5,000 cd
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	14 W
Lamp Current (Nom)	110 mA
Wattage Equivalent	120 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	75 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	PAR38

Essential LEDspot PAR

Approval and Application


Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

Product Data

Order product name	LED 14-120W PAR38 827 25D
Full product name	LED 14-120W PAR38 827 25D
Full product code	692234190609100
Local code description	PAR38LED14-120W


Order code	929002339107
Material Nr. (12NC)	929002339107
Local order code	PAR38LED14-120W
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.385 kg
EAN/UPC - Product/Case	6922341906091
Numerator - Packs per outer box	6
EAN/UPC - Case	6922341906107

Dimensional drawing




Product	D	C
LED 14-120W PAR38 827 25D	125 mm	133 mm

Photometric data



Accent Lighting - Spots
14-120W PAR38 827 25D
125mm
133mm
12°
1000mm
125mm




Accent Lighting Spots - LED 14-120W PAR38 827 25D

Light Distribution Diagram - LED 14-120W PAR38 827 25D

Essential LEDspot PAR

Photometric data



Spectral Power Distribution Colour - LED 14-120W PAR38 827 25D

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED 14-120W PAR38 827 25D

