



# Energy Saver GU24

## EL/mdTQS 18W GU24

Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

### Product data


General Information	
Cap-Base	GU24
Nominal lifetime	10,000 hour(s)
Switching Cycle	5,000
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,250 lm
Luminous Efficacy (rated) (Nom)	67 lm/W
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	459
Chromaticity Coordinate Y (Nom)	412
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	50 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	18.0 W

Lamp Current (Nom)	290 mA
Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	EL/mdTQS
Approval and Application	
Mercury (Hg) Content (Max)	2 mg
Energy Consumption kWh/1000 h	18 kWh
Product Data	
Order product name	18 W (75 W) Compact fluorescent Spiral bulb
Full product name	EL/mdTQS 18W GU24
Order code	454207
Material Nr. (12NC)	929689791301
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.070 kg
EAN/UPC - Product/Case	046677454203

Energy Saver GU24

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677454208

Dimensional drawing



Product	D (max)	C (max)	F (max)
18 W (75 W) Compact fluorescent Spiral bulb	56.5 mm	104.0 mm	47 mm

