

# PHILIPS

Bulb 68W A60S E27

LED

3000K

770lm

15000h

8718699651633



## A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

### High quality LED light that lasts for decades

- Reduced glare. Increased comfort.

# Highlights

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Contains no mercury

### EyeComfort with Interlaced optics

Interlaced optics technology enhances the overall lighting experience in your every-day life. Imprinted with 3D patterns to help diffuse light, the micro-lens technology produce an

even distribution of light which reduces glare significantly. This illumination is not only a soft and uniform light which brings more comfort to your eyes, but it also cleverly redistributes light for less glaring illumination in the lit area.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Frosted
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Bulb dimensions

- Height: 11 cm
- Width: 6 cm

## Design and finishing

- Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000 h
- Ambient temperature range: -20 to +45 °C

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 910 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 930 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 910 lm
- Luminous Efficacy (rated) (Nom): 113 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Efficacy: 113 lm/W
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8718699651633
- EOC: 871869965163300
- Product title: LEDBulb 8W E27 930 230V 1PF/6 AU

## Power

- Power Factor (Fraction): 0.5

## Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage: 8 W
- Wattage equivalent: 76 W
- Power Consumption: 8 W

## Product dimensions and weight

- Length: 11 cm

8718699651633

#### Rated values

- Rated lifetime: 15,000 h

#### Technical specifications

- Frequency: 50-60 Hz
- Dimmable: No
- Cap-Base: E27

#### Packaging dimensions & weight

- EAN/UPC - product: 8718699651633
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm



Issue date: 2024-11-21  
Version: 0.174

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)