

PHILIPS

Filament Bulb Clear
40W A60 E27

UltraEfficient

4000K

485lm

50000h

8719514454958



Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Better for your wallet and your planet
- Long life bulb - Lasts up to 50 years

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Clear
- Dimmable: No
- Bulb Finish: Clear
- Bulb Material: Glass

Bulb dimensions

- Height: 10.5 cm
- Width: 6 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 h
- Ambient temperature range: -20 to +45 °C

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 485 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 840 | CCT of 4000K
- Correlated Color Temperature (Nom): 4000 K
- Luminous Flux: 485 lm
- Luminous Efficacy (rated) (Nom): 210 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: UltraEfficient, EyeComfort

Other characteristics

- Efficacy: 210 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514454958
- EOC: 871951445495800
- Product title: LED CLA 40W A60 E27 4000K CL EELA SRT AU

Power

- Power Factor (Fraction): 0.4

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 2.3 W
- Wattage equivalent: 40 W
- Power Consumption: 2.3 W

Product dimensions and weight

- Length: 10.5 cm

Rated values

- Rated lifetime: 50,000 h

Technical specifications

- Frequency: 50–60 Hz
- Dimmable: No
- Cap-Base: E27

Packaging dimensions & weight

- EAN/UPC – product: 8719514454958
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 14.6 cm
- Length: 6.6 cm
- Width: 6.4 cm
- Material number (12NC):
929003066519



Issue date: 2024-06-14
Version: 0.46

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com