

PHILIPS

Capsule 40W G9
G9

LED

3000K

470lm

15000h



8720169301719



A familiar beam meets an innovative design

This Mains voltage LED capsule provides bright, all around, white light.

High quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen capsules

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces halogen capsules



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen capsules.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe - old value
- Socket: G9
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions

- Height: 5.2 cm
- Width: 1.6 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 320 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 470 lm

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 127 lm/W

Packaging information

- EAN: 8720169301719
- EOC: 872016930171900
- Product title: LED 40W G9 WH ND SRT6

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage: 3.7 W
- Wattage equivalent: 40 W
- Energy Efficiency Label (EEL): E

Product dimensions and weight

- Length: 5.2 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1932581

Packaging dimensions & weight

- EAN/UPC - product: 8720169301719
- Net weight: 0.01 kg
- Gross weight: 0.01 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm
- Material number (12NC):
929003790901



Issue date: 2024-08-31
Version: 0.228

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com