



# **Specification Sheet**


# **UID8470**Zigbee Green Power switch

- · No wiring and power connections required so easy to install.
- Low mechanical force required to operate the device (typically less than 8 Newton).
- Indoor distance that can be covered is typically 10m. for line-of-sight installations. When there are walls this will be reduced depending on the type and thickness of the walls.

# **UID8470**

- · Provides switch and dim functionality.
- Wireless communication based on the ZigBee Pro standard (IEEE 802.15.4, WPAN). There is no need to connect to any electrical power supply as the device is battery powered.
- When a button is pressed, or released, a message is sent including a unique 32-bit identifier which prevents interferences with other devices.
- Briefly pressing the upper or lower part of the device either switches lights On or Off.
- A press and hold action engages the dim-up or dim-down function.
- The device is Interact ready and can be easily linked to a wireless standalone or connected lighting system.
- The devices are easy to install and use. Additional information can be found in the appropriate installation instructions.

## **Dimensional drawing**



# **Specifications**

Communication					
Wireless	Zigbee PRO Green Power IEEE 802.15.4 WPAN				
Data rate	250 kbps				
Carrier frequency	2.4 GHz				
Transmission distances (typic	al values)*				
Indoor (plasterboard)	10 m (33 ft); max. 3 walls				
Indoor reinforced concrete	7 m (23 ft); max 1 wall/ ceiling				
Physical					
Dimensions (H x W x D)	81 x 81 x 14 mm (3.19 x 3.19 x 0.55 in)				
Weight	0.098 kg (0.22 lb)				
Housing	Polycarbonate				
Color	White (similar to RAL9000)				
Lifetime	>50,000 actuations				
Environment					
Temperature (operating)	-25 to 65 °C (-13 to 149 °F)				
Relative humidity (operating)	0% to 95% (non-condensing				
Temperature (storage and transport)	-25 to 65 °C (-13 to 149 °F)				
Relative humidity (storage and transport)	0% to 95% (non-condensing				

 $<sup>^{\</sup>ast}$  distance is largely influenced by the wall/ceiling material and the angle that the transmitted signal is intersecting with. Note:fire-safety walls, elevator shafts and so on are considered asshielding.

# Compliances and approvals

Protection rating	IP20		
Electromagnetic compatibility (EMC)	EN 61000-6-2:2005 EN 61000-6-4:2007+A1:2011		
Quality standard	ISO9001		
Environmental standard	ISO14001, CE2522		
Restriction of Hazardous Substances (RoHS)	2011/65/EU Annex 2015/863/EU		
Wireless			
Radio Equipment Directive	RED 2014/53/EU		
Electronic compatibility and radio spectrum matters (ERM)	EN 301489-1:V2.2.0 EN 301489-17:V3.2.0		

ETSI EN 300 328: V1.8.1



systems



Wideband transmission



## Packing data

Туре	Dimensions C	Qty	Material	Weight	
				net	gross
Single pack	205 x 95 x 95 mm (80.7 x 37.4 x 37.4 in)	10	Cardboard	0.6 kg (1.3 lb)	0.7 kg (1.5 lb)

# Ordering data

Туре	MOQ	Ordering number	EAN1	EAN2	EOC
UID8470/10 ZGP Switch Dim 2B	10	9137 010 55703	8719514 273771	8719514 273795	273771 00

