

PHILIPS

UltraEfficient LED

**REAL
PROs
REAL
QUALITY**

Real pros support sustainability goals with
**high-performance,
ultra-efficient LED**

Meet the extended Philips UltraEfficient LED range —
our most energy-efficient LED lamps yet



**A-class and
B-class**



¹This icon has been developed by Signify and is used as a self-certification for the Philips UltraEfficient lamps and luminaires meeting the standards of EU Energy Label A or B (lamps) and tier 3 in IEA 4E SSL ANNEX (luminaires).

Step into a brighter, more sustainable future

Many companies today are trying to reduce their energy costs – and their corporate carbon footprint. Did you know that lighting on average represents up to 10% of electricity consumption in buildings?¹

Switching to energy-efficient LED solutions can really make a difference!

Meet our most energy-efficient LED lights yet

Thanks to our cutting-edge technology breakthrough, Philips ultra-efficient LED bulbs, candles, spots, tubes and HID replacement lamps not only offer superior light quality, but also allow your customers to immediately save from 44% to 65% energy compared with standard alternative products.²

Thanks to these savings and the longer service life of LEDs, you can offer attractive payback times! On top of this, the switch to ultra-efficient LEDs also contributes to improved sustainability.

And ultra-efficient LED has something to offer for you too: Although the products require less maintenance and replacement, your customer's higher investment brings you a higher profit per light point!





Start saving energy and money now!
Visit the [website](#) for more information.

¹ U.S. commercial sector electricity consumption by major end uses, 2022, according to the U.S. Energy Information Administration [Annual energy outlook 2023](#) (table 5).
² Energy savings of the UltraEfficient products compared with the Philips standard alternative products: Philips MASTER LEDbulb UE 4W A60 saves 50% compared to Philips CorePro LEDbulb A60 60W; Philips MASTER LEDtube UE EELA 1500mm 17.6W saves 44% compared to Philips CorePro LEDtube EM/mains Ultra Output 1500mm 31.5W operating on direct mains; Philips MASTER LEDspot UE 50W EELA saves 45% compared to Philips LEDspot GU10 50W; Philips MASTER SON-T UE 42.8W saves approx. 65% energy compared to Philips SON-T 100W E40 lamps (incl. 10W ballast losses).

MASTER LEDbulbs UltraEfficient



New: Ultra-efficient A-class candles, lusters and dimmable bulbs



More reasons to upgrade

- Ultra-efficient with 210 lm/W
- Very high-quality and comfortable light
- No flicker, reduced glare, CRI 80
- Perfect solution for offices, residential, and hospitality applications
- Available in full range, from 40W to 100W replacement
- Now available in 2700K, 3000K and 4000K

Product highlights

Available in clear and frosted glass versions, the dimmable A-class bulbs convince with innovative features pioneering sustainable lighting.

Ever seen a dimmable A-class bulb? Here you go.

Thermal


- Optimized filament position for better thermal control

Optics

- Filament orientation designed for most efficient light output

LED design

- High-efficiency phosphor
- Optimally balanced color point (CRI 80) in line with EU Ecodesign light source regulation
- Industry-leading LED chip for most efficient conversion of input power into light output



Driver upgrade

- Optimization of driver architecture and component design to improve efficiency
- More compact size to fit into E-cap

¹ This icon has been developed by Signify and is used as a self-certification for the Philips UltraEfficient lamps and luminaires meeting the standards of EU Energy Label A or B (lamps) and tier 3 in IEA 4E SSL ANNEX (luminaires). ² Philips MASTER LEDbulb UE 4W A60 compared to Philips CorePro LEDbulb 8W A60 (referred to as standard LED bulb). The lights are on for an average of 12 hours per day, 365 days of the year (4,380 hours annually). The average energy cost is 0.252 €/kWh according to the latest Eurostat report, and it is calculated for the non-household consumers in Europe, valid in H1 2023, based on 27 countries, all taxes and levies included. The data presented is an illustrative forecast based on a proprietary model developed by Signify to help customers understand the impact of lighting on the environment. Signify's „Green Switch conventional light point conversion model“ uses input from numerous sources, references, and data points (available upon request) to generate a simulated view of a given market's energy consumption, but the accuracy of which cannot be verified. The thousand separator is a comma (,) and the decimal separator is a period (.). ³ Based on the emission factor of 0.3 kg/kWh, Europe average. Greenhouse gases emitted per unit of generated electricity, measured in grams of CO₂ equivalents per kilowatt-hour as of 2023 based on Our World in Data. ⁴ Charging a phone once a day will use about 0.15 kWh of electricity per month and 1.83 kWh of electricity per year. Click here for more details.

Shining a light on efficiency

When upgrading from standard LED bulbs, your customers can expect a full return on investment in only 0.7 years. A typical restaurant will save € 549 per year by replacing 100 units of 8W standard LED bulbs with 4W ultra-efficient LED bulbs.²

	Standard LED bulb ²	A-class LED bulb
Lifetime (L70)	15,000 hrs	50,000 hrs
Lamp wattage	8W	4W
Total installation savings/year ²		€ 549
Payback period ²		0.7 years

Number of lamps	100	Energy costs	0.25 €/kWh	Lamp cost/year	€ 0.59	Total costs/year/lamp	€ 5.32
Burning hours per year	4,380 hrs	Replacement cost/year/lamp	€ 0.35	Energy costs/year/lamp	€ 4.38		

Compared to a standard LED bulb², a new Philips LED bulb UE can reduce CO₂ emission by 3310 kg over its lifetime³ and its annual energy savings can charge 9 smartphones for a whole year.⁴

Order information

Product type	Bulb shape	Socket	Bulb finish	Power	Lumen output		Efficacy	CRI	Color temp.	Lifetime	Dimmable	EEL	EOC code											
					W	lm																		
MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	A60	E27	Clear Glass	40	2.3	485	210	80	2700	50,000	no	A	8720169											
MAS LEDBulbND2.3-40W E27 830 A60 CL G UE					2.3	485							3000	25404600										
MAS LEDBulbND2.3-40W E27 840 A60 CL G UE					2.3	485							4000	18837200										
MAS LEDBulbND4-60W E27 827 A60 CL G UE					4	840							2700	18845700										
MAS LEDBulbND4-60W E27 830 A60 CL G UE					4	840							3000	25412100										
MAS LEDBulbND4-60W E27 840 A60 CL G UE					4	840							4000	18853200										
MAS LEDBulbND5.2-75W E27 827 A60 CL G UE					5.2	1,095							2700	18861700										
MAS LEDBulbND5.2-75W E27 830 A60 CL G UE					5.2	1,095							3000	25420600										
MAS LEDBulbND5.2-75W E27 840 A60 CL G UE					5.2	1,095							4000	18869300										
MAS LEDBulbND7.3-100W E27 827 A60 CL G UE					7.3	1,535							2700	18877800										
MAS LEDBulbND7.3-100W E27 830 A60 CL G UE					7.3	1,535							3000	25428200										
MAS LEDBulbND7.3-100W E27 840 A60 CL G UE					7.3	1,535							4000	18885300										
MAS LEDCandleND2.3-40W E14 827 B35 CL G UE					B35	E14							Clear Glass	40	2.3	485	210	80	2700	50,000	no	A	18893800	
MAS LEDCandleND2.3-40W E14 840 B35 CL G UE															2.3	485							4000	18895200
MAS LEDLusterND2.3-40W E14 827 P45 CL G UE															2.3	485							2700	18897600
MAS LEDLusterND2.3-40W E14 840 P45 CL G UE															2.3	485							4000	18903400
MAS LEDLusterND2.3-40W E27 827 P45 CL G UE	P45	E27	Clear Glass	40	2.3	485	210	80	2700	50,000	no	A	18899000											
MAS LEDLusterND2.3-40W E27 840 P45 CL G UE					2.3	485							4000	18905800										
MAS LEDBulbND4-60W E27 827 ST64 CL G UE	ST64	E27	Clear Glass	60	4	840	210	80	2700	50,000	no	A	20274000											
MAS LEDBulbND4-60W E27 827 G95 CL G UE					4	840							2700	20276400										
MAS LEDBulbND4-60W E27 840 G95 CL G UE					4	840							4000	20278800										
MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	A60	E27	Frosted Glass	40	2.3	485	210	80	2700	50,000	no	A	18833400											
MAS LEDBulbND2.3-40W E27 830 A60 FR G UE					2.3	485							3000	25408400										
MAS LEDBulbND2.3-40W E27 840 A60 FR G UE					2.3	485							4000	18841900										
MAS LEDBulbND4-60W E27 827 A60 FR G UE					4	840							2700	18849500										
MAS LEDBulbND4-60W E27 830 A60 FR G UE					4	840							3000	25416900										
MAS LEDBulbND4-60W E27 840 A60 FR G UE					4	840							4000	18857000										
MAS LEDBulbND5.2-75W E27 827 A60 FR G UE					5.2	1,095							2700	18865500										
MAS LEDBulbND5.2-75W E27 830 A60 FR G UE					5.2	1,095							3000	25424400										
MAS LEDBulbND5.2-75W E27 840 A60 FR G UE					5.2	1,095							4000	18873000										
MAS LEDBulbND7.3-100W E27 827 A60 FR G UE					7.3	1,535							2700	18881500										
MAS LEDBulbND7.3-100W E27 830 A60 FR G UE					7.3	1,535							3000	25432900										
MAS LEDBulbND7.3-100W E27 840 A60 FR G UE					7.3	1,535							4000	18889100										
MAS LEDBulb D 4-60W E27 827 A60 CL G UE					A60	E27							Clear Glass	60	4	840	210	80	2700	50,000	yes	A	24864900	
MAS LEDBulb D 4-60W E27 830 A60 CL G UE															4	840							3000	24868700
MAS LEDBulb D 4-60W E27 827 A60 FR G UE															4	840							2700	24866300
MAS LEDBulb D 4-60W E27 830 A60 FR G UE															4	840							3000	24870000

UltraEfficient T8 LED tubes



**New:
The first UltraEfficient
MASTER Value LEDtube**

More options, more savings

Welcome the new Philips MASTER Value LEDtube UltraEfficient – your solution for upgrading more price-sensitive customers to ultra-efficient LED. Thanks to the cost-efficient design, high energy efficiency and long service life, the new LED tube can convince with a payback time of less than 2 months, when upgrading from fluorescent tubes (banned since 2023)!²

For even higher lifetimes and energy savings, choose Philips MASTER LEDtubes UltraEfficient – our most efficient LED tube.

Philips MASTER LEDtube UE

Saves 75% in energy costs, compared to fluorescent tubes²

Very long lifetime of 100,000 hours (L70) – 5x longer than fluorescent tubes²

Less than 5 months payback time, compared to fluorescent tubes²

10-year warranty³

Product highlights

Rotatable end cap that gives light where needed

Plastic design makes it truly shatterproof according to IEC 61549 standards

210 lm/W ultra efficiency for an incredible A-class energy-efficiency rating^{3,4}

Philips MASTER Value LEDtube UE

Saves 69% in energy costs, compared to fluorescent tubes²

Long lifetime of 75,000 hours (L70) – more than 3x longer than fluorescent tubes²

Less than 2 months payback time, compared to fluorescent tubes²

5-year warranty

Product highlights

Glass platform with 190° beam angle to ensure light uniformity

185 lm/W energy efficiency, enabling a B-class energy-efficiency rating⁴

High lumen output of as much as 4,100 lm ensures bright light in various applications

New

Cost and energy savings right from the start

When upgrading from fluorescent tubes, your customers can expect a full return on investment in only 4 months. Any application that requires the light to be switched on all the time will save € 11,848 by replacing 100 units of 58W fluorescent tubes with 17.6W ultra-efficient MASTER LEDtubes UE.²

	Standard LED tube ²	MASTER LEDtube UE	MASTER Value LEDtube UE	Fluorescent tube ²	MASTER LEDtube UE	MASTER Value LEDtube UE
Lifetime (L70)	50,000 hrs >	100,000 hrs	75,000 hrs	20,000 hrs >	100,000 hrs	75,000 hrs
Lamp wattage	25.9W >	17.6W	22.1W	58W >	17.6W	22.1W
Total installation savings/year ²		€ 1,662	€ 843		€ 11,848	€ 11,029
Payback period ²		2.6 years	1.9 years		0.4 years	0.1 years

General info	Number of lamps	100	Burning hours per year	8,760 hrs	Energy costs	0.25 €/kWh		
MASTER LEDtube UE	Replacement cost/year/lamp	€ 0.44	Lamp cost/year	€ 3.72	Energy costs/year/lamp	€ 38.54	Total costs/year/lamp	€ 42.70
MASTER Value LEDtube UE	Replacement cost/year/lamp	€ 0.58	Lamp cost/year	€ 1.91	Energy costs/year/lamp	€ 48.40	Total costs/year/lamp	€ 50.89

Compared to a standard LED tube², a new Philips MASTER LEDtube UE can **reduce CO₂ emission by 249 kg over its lifetime⁵ – and its annual energy savings can charge 4 laptops for a year!⁶**

Compared to a fluorescent tube², a new Philips MASTER LEDtube UE can **reduce CO₂ emission by 1632 kg over its lifetime⁵ – and its annual energy savings can charge 24 laptops for a year!⁶**

Compared to a standard LED tube², a new Philips MASTER Value LEDtube UE can **reduce CO₂ emission by 85 kg over its lifetime⁵ – and its annual energy savings can charge 2 laptops for a year!⁶**

Compared to a fluorescent tube², a new Philips MASTER Value LEDtube UE can **reduce CO₂ emission by 1122 kg over its lifetime⁵ – and its annual energy savings can charge 22 laptops for a year!⁶**

Order information

Product type	Power	Lumen output	Efficacy	Beam angle	CRI	Color temp.	Lifetime	EEL	EOC code
MASTER LEDtube UE	W	lm	lm/W			K	hrs		8719514
MAS LEDtube 1200mm UE 11.9W 840 T8 EELA	11.9	2,500	210	160°	80	4000	100,000	A	43166900
MAS LEDtube 1500mm UE 17.6W 840 T8 EELA	17.6	3,700							43168300
MAS LEDtube 1200mm UE 13.5W 840 T8	13.5	2,500	185			75,000	B	33972900	
MAS LEDtube 1200mm UE 13.5W 865 T8								33974300	
MAS LEDtube 1500mm UE 20W 840 T8	20	3,700		33976700					
MAS LEDtube 1500mm UE 20W 865 T8				33978100					
MASTER LEDtube UE									8720169
MAS LEDtube 1200mm UE 11.9W 865 T8 EELA	11.9	2,500	210	160°	80	6500	100,000	A	26959000
MAS LEDtube 1500mm UE 17.6W 865 T8 EELA	17.6	3,700							26961300
New: MASTER Value LEDtube UE									8720169
New MAS LEDtube VLE 1200mm UE 14W 840 T8	14	2,600	185	190°	80	4000	75,000	B	31671300
New MAS LEDtube VLE 1500mm UE 22.1W 840 T8	22.1	4,100							31675100

¹ This icon has been developed by Signify and is used as a self-certification for the Philips UltraEfficient lamps and luminaires meeting the standards of EU Energy Label A or B (lamps) and tier 3 in IEA 4E SSL ANNEX (luminaires). ² Fluorescent tube calculations are based on Philips MASTER LEDtube UE EELA 1500mm 17.6W/ Philips MASTER Value LEDtube UE 1500mm 22.1W (both operating on direct mains) compared to Philips MASTER TL-D 1500mm 58W (operating on electro-magnetic ballast with 14W ballast loss; banned since 2023). Standard LED tube calculations are based on Philips MASTER LEDtube UE EELA 1500mm 17.6W/Philips MASTER Value LEDtube UE 1500mm 22.1W compared to Philips CorePro LEDtube EM/mains Ultra Output 1500mm 25.9W (all operating on direct mains). The lights are on for an average of 24 hours per day, 365 days of the year (8,760 hours annually). The average energy cost is 0.252 €/kWh according to the latest Eurostat report, and it is calculated for the non-household consumers in Europe, valid in H12023, based on 27 countries, all taxes and levies included. The data presented is an illustrative forecast based on a proprietary model developed by Signify to help customers understand the impact of lighting on the environment. Signify's „Green Switch conventional light point conversion model“ uses input from numerous sources, references, and data points (available upon request) to generate a simulated view of a given market's energy consumption, but the accuracy of which cannot be verified. The thousand separator is a comma (,) and the decimal separator is a period (.). ³ For Philips MASTER LEDtubes UE EELA ⁴ According to the updated European Energy Labelling Regulation (09/2021) ⁵ Based on the emission factor of 0.3 kg/kWh, Europe average. Greenhouse gases emitted per unit of generated electricity, measured in grams of CO₂ equivalents per kilowatt-hour as of 2023 based on Our World in Data. ⁶ Under typical daily usage, laptops use 0.055 kWh per day and 20.24 kWh per year, on average. [Click here](#) for more details.

MASTER LEDspot UltraEfficient GU10



New: Dimmable ultra-efficient A-class LEDspot



Saves 50% in energy costs²



Very long lifetime of 50,000 hours (L70) — more than 3 x longer²



5.1 years payback time³



5-year warranty

Product highlights

With new dimmable versions available, the Philips MASTER LEDspot UltraEfficient GU10 now offers even more choice on the way to more sustainable lighting.

LED design

- Special LED design with compact size fit for small size spot lights
- High efficiency phosphor
- Best LED system integration design to enable highest driver and optical efficiency



Optics

- Special lens design to optimize light output efficiency

Driver

- Revolutionary driver design boosts energy efficiency, dramatically reducing power consumption
- **New dimmable spots:**
 - Phase cut dimmer detection
 - Leading/trailing edge dimmer
 - Improved dimmer compatibility

Thermal

- Excellent thermal management system for very long lifetime of 50,000 hours

Unlock the potential of greater energy savings

When upgrading from standard LED spots, your customers can expect a full return on investment in just above 5 years. A typical small shop will save € 265 a year by replacing 100 standard LED spots (4.6W) with ultra-efficient A-class GU10 LED spots.²

	Standard LED spot ¹	MASTER LEDspot UE					
Lifetime (L70)	15,000 hrs	50,000 hrs					
Lamp wattage	4.6W	2.1W					
Total installation savings/year²		€ 265					
Payback period²		5.1 years					
Number of lamps	100	Energy costs	0.25 €/kWh	Lamp cost/year	€ 1.57	Total costs/year/lamp	€ 4.59
Burning hours per year	3,600 hrs	Replacement cost/year/lamp	€ 0.48	Energy costs/year/lamp	€ 2.54		

Compared to a standard LED spot², a new Philips MASTER LEDspot GU10 UE can reduce CO₂ emission by 3750 kg over its lifetime³ and its annual energy savings can charge 5 smartphones for a whole year.⁴

Order information

Product type	Cap	Power	Lumen output	Replaced wattage	MBCP	Color temp.	Beam angle	Dimmable	Lifetime	EEL	EOC code
		W	lm	W	cd	Kv			hrs		8719514
MAS LEDspot UE 2.1-50W GU10 ND 827 EELA						2700					3634602
MAS LEDspot UE 2.1-50W GU10 ND 830 EELA	GU10	2.1	375	50	680	3000	36	no	50,000	A	3610002
MAS LEDspot UE 2.1-50W GU10 ND 840 EELA						4000					3610102
New											8720169
New MAS LEDspot UE 2.1-50W GU10 DIM 827 EELA						2700					30792600
New MAS LEDspot UE 2.1-50W GU10 DIM 830 EELA	GU10	2.1	375	50	650	3000	36	yes	50,000	A	30794000
New MAS LEDspot UE 2.1-50W GU10 DIM 840 EELA						4000					30796400

¹ This icon has been developed by Signify and is used as a self-certification for the Philips UltraEfficient lamps and luminaires meeting the standards of EU Energy Label A or B (lamps) and tier 3 in IEA 4E SSL ANNEX (luminaires).

² Philips MASTER LEDspot UE 50W EELA compared to Philips LEDspot GU10 50W (referred to as standard LED spot). The lights are on for an average of 12 hours per day, 300 days of the year (3,600 hours annually). The average energy cost is 0.252 €/kWh according to the latest Eurostat report, and it is calculated for the non-household consumers in Europe, valid in H12023, based on 27 countries, all taxes and levies included. The data presented is an illustrative forecast based on a proprietary model developed by Signify to help customers understand the impact of lighting on the environment. Signify's „Green Switch conventional light point conversion model“ uses input from numerous sources, references, and data points (available upon request) to generate a simulated view of a given market's energy consumption, but the accuracy of which cannot be verified. The thousand separator is a comma (,) and the decimal separator is a period (.).

³ Based on the emission factor of 0.3 kg/kWh, Europe average. Greenhouse gases emitted per unit of generated electricity, measured in grams of CO₂ equivalents per kilowatt-hour as of 2023 based on Our World in Data.

⁴ Charging a phone once a day will use about 0.15 kWh of electricity per month and 1.83 kWh of electricity per year. [Click here](#) for more details.

MASTER LED SON-T UltraEfficient



New: Updated size for perfect fit



Saves 65% in energy costs²



Very long lifetime of 50,000 hours (L70)



2.7 years payback time²




5-year warranty

Sustainability meets profitability

Welcome the first ultra-efficient LED SON-T lamps to replace conventional HID lamps. A solution that takes replacing conventional HID with high-efficiency, cost-saving LEDs to the next level. With a quick payback, these lamps offer all the benefits of LED lighting and provide immediate savings for a small investment. They offer the same lamp size and light distribution and can be easily retrofitted into existing SON-T lamps while providing a similar look and feel.

Product highlights

The Philips MASTER LED SON-T UltraEfficient offers all the benefits of LED lighting — and more.



Brighter roads, lighter energy bills

When upgrading from conventional HID lamps, your customers can expect a full return on investment in 2.7 years. A typical installation will save € 6,027 by replacing 100 units of 100W conventional HID lamps with 42.8W ultra-efficient A-class LED SON-T.²

	Conventional HID ²	MASTER LED SON-T UE
Lifetime (L70)	20,000 hrs	50,000 hrs
Lamp wattage	100W	42.8W
Total installation savings/year ²		€ 6,027
Payback period ²		2.7 years

Number of lamps	100	Energy costs	0.25 €/kWh	Lamp cost/year	€ 13.12	Total costs/year/lamp	€ 57.81
Burning hours per year	4,100 hrs	Replacement cost/year/lamp	€ 0.82	Energy costs/year/lamp	€ 43.87		

Compared to a conventional HID lamp², a new Philips MASTER LED SON-T UE can reduce CO₂ emission by 1043 kg over its lifetime³ and its annual energy savings can power an e-bike for 3,556 kilometers!⁴

Order information

Product type	Power	Lumen output	Replaced wattage	CRI	Socket	Color temp.	Lifetime	EEL	EOC code
	W	lm	W			K	hrs		
MAS LED SON-T UE M 4Klm 19W 740 E27	19	4,000	50	70	E27	4000	50,000	A	37419500
MAS LED SON-T UE M 6Klm 28.5W 740 E27	29	6,000	70		E40				37421800
MAS LED SON-T UE M 9Klm 42.8W 740 E40	43	9,000	100		E27				37423200
MAS LED SON-T UE M 3.6Klm 19W 727 E27	19	3,600	50		E27	2700		B	37425600
MAS LED SON-T UE M 5.4Klm 28.5W 727 E27	29	5,400	70						24037700
MAS LED SON-T UE M 8Klm 42.8W 727 E40	43	8,000	100						E40

¹ This icon has been developed by Signify and is used as a self-certification for the Philips UltraEfficient lamps and luminaires meeting the standards of EU Energy Label A or B (lamps) and tier 3 in IEA 4E SSL ANNEX (luminaires).

² Philips MASTER SON-T UE 42.8W compared to Philips SON-T 100W E40 lamps (incl. 10W ballast losses). The lights are on for an average of 12 hours per day, 365 days of the year (4,100 hours annually). The average energy cost is 0.252 €/kWh according to the latest Eurostat report, and it is calculated for the non-household consumers in Europe, valid in H12023, based on 27 countries, all taxes and levies included. The data presented is an illustrative forecast based on a proprietary model developed by Signify to help customers understand the impact of lighting on the environment. Signify's „Green Switch conventional light point conversion model“ uses input from numerous sources, references, and data points (available upon request) to generate a simulated view of a given market's energy consumption, but the accuracy of which cannot be verified. The thousand separator is a comma (,) and the decimal separator is a period (.).

³ Based on the emission factor of 0.3 kg/kWh, Europe average. Greenhouse gases emitted per unit of generated electricity, measured in grams of CO₂ equivalents per kilowatt-hour as of 2023 based on Our World in Data.

⁴ Average annual distance of one e-bike sharing is 10,000 km (click here for more details). One e-bike annual charging is 225 kWh/km (click here for more details).

You and Signify – a reliable partnership

Signify, previously known as Philips Lighting, is the world leader in connected LED lighting systems, software and services. We proudly market the best lighting brands in the world, including Philips and Interact.

Close cooperation before, during and after projects is important to us. Our local service teams make sure you always get the competent support and information you need. We are closely working with local wholesalers to offer you flexible and on-time delivery – and product availability you can rely on.

To help you stay on top of your game the [Signify Lighting Academy](#) offers a comprehensive range of educational resources for you to grow your expertise and get certified.

Our global brands

PHILIPS

The Philips brand stands for quality and energy-efficiency in light. For over 125 years, Philips products have been at the forefront of innovation.

Today Philips is recognized as the leading brand in lighting.

interact

Interact is the brand of our IoT software and platform that manages smart lighting systems and the data that those systems collect.

Smart, simple and scalable, Interact software can be used in a wide range of application areas, from small offices to entire cities.

We aim to help you work faster, better, smoother. How? Check:



Signify



Driven by responsible innovation

Signify and Mercedes-AMG PETRONAS F1 Team are driven by a shared passion for technology and the desire to push the boundaries of what is possible.

Our innovations in lighting support the team's ambition to become one of the world's most sustainable in sport, serve the well-being and performance of the team, and deliver powerful experiences for fans, trackside and at home.

[Learn more at](#)

Signify is Official Lighting Partner of
Mercedes-AMG PETRONAS F1 Team

Signify



Official Lighting Partner

AMG
PETRONAS
FORMULA ONE TEAM



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

www.philips.com/ultraefficientprof