



PILA LED Ceiling

PILA Ceiling RD 10W 4000K W 06

PILA Ceiling – LED Module, system flux 1100 lm – 840 neutral white – 10 W

Benefits

- Energy efficient
- Wide application range



CRI



15,000 h



Non-dimmable



10,000x



Product data

General information

Light source color	840 neutral white
Light source replaceable	-
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Emergency Lighting	-
Optic type	-
Control interface	No
Connection	Connector
Protection class IEC	Safety class I
Mounting	-
CE mark	Yes
EU RoHS compliant	Yes
Constant light output	No
Number of products on MCB of 16 A type B	-
Service tag	-
Product family code	PILA Ceiling

Operating and Electrical

Input Voltage	220-240 V
Input Frequency	50 to 60 Hz
Inrush current	-
Inrush time	-
Power Factor (Min)	> 0.9
Surge Protection (KV)	-

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Material	Polycarbonate
Optical cover/lens material	-
Optical cover/lens finish	-
Overall length	-
Overall width	-
Overall height	68 mm
Diameter	250 mm
Color	White
Accessory	-

Approval and Application

Ingress protection code	IP20
Mech. impact protection code	-

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1100 lm
Initial LED luminaire efficacy	110 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	> 80
Initial chromaticity	-
Initial input power	10 W



Over Time Performance (IEC Compliant)

Lifetime L65B50	15,000 h
-----------------	----------


Application Conditions

Performance ambient temperature Tq	-
------------------------------------	---

Product Data

Full product code	-
Order product name	PILA Ceiling RD 10W 4000K W 06
EAN/UPC - Product	8727900967807
Order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	915005778323
Net Weight (Piece)	-

Dimensional drawing





PILA LED Ceiling

PILA Ceiling RD 17W 4000K W 06

PILA Ceiling – LED Module, system flux 1900 lm – 840 neutral white – 17 W

Benefits

- Energy efficient
- Wide application range



CRI



15,000 h



Non-dimmable



10,000x



Product data

General information

Light source color	840 neutral white
Light source replaceable	-
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Emergency Lighting	-
Optic type	-
Control interface	No
Connection	Connector
Protection class IEC	Safety class I
Mounting	-
CE mark	Yes
EU RoHS compliant	Yes
Constant light output	No
Number of products on MCB of 16 A type B	-
Service tag	-
Product family code	PILA Ceiling

Operating and Electrical

Input Voltage	220-240 V
Input Frequency	50 to 60 Hz
Inrush current	-
Inrush time	-
Power Factor (Min)	> 0.9
Surge Protection (KV)	-

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Material	Polycarbonate
Optical cover/lens material	-
Optical cover/lens finish	-
Overall length	-
Overall width	-
Overall height	68 mm
Diameter	320 mm
Color	White
Accessory	-

Approval and Application

Ingress protection code	IP20
Mech. impact protection code	-

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1900 lm
Initial LED luminaire efficacy	112 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	> 80
Initial chromaticity	-
Initial input power	17 W



Over Time Performance (IEC Compliant)

Lifetime L65B50	15,000 h
-----------------	----------

Application Conditions

Performance ambient temperature Tq	-
------------------------------------	---

Product Data

Full product code	-
Order product name	PILA Ceiling RD 17W 4000K W 06
EAN/UPC - Product	8727900967821
Order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	915005778923
Net Weight (Piece)	-

Dimensional drawing

