

# **PILA LED panel**

# PILA RC007B LED40S/840 PSU I W60L60 NOC

PILA Panel - system flux 4000 lm - 840 neutral white

## **Benefits**

- Applicable for wide range of applications
- Supports energy saving
- Reliable quality



# **Product data**

### General information

Lamp family code	LED40S [LED Module, system flux 4000 lm]
Light source color	840 neutral white
Light source replaceable	-
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Emergency Lighting	-
Optic type	-
Control interface	No
Connection	Fly wire
Protection class IEC	Safety class I
Mounting	-
CE mark	Yes
EU RoHS compliant	Yes
Constant light output	No
Number of products on MCB of 16 A type B	-
URG <19	No
Product family code	RC007C [PILA Panel]
Operating and Electrical	
Input Voltage	220-240 V
Input Frequency	50 to 60 Hz
Inrush current	-
Inrush time	-
Power Factor (Min)	> 0.9



Surge Protection (KV)	-
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Material	Steel
Optical cover/lens material	Polystyrene
Optical cover/lens finish	Opal
Overall diameter	595 mm
Overall height	595 mm
Overall height 1	33 mm
Color	White
Accesory	Suspension set, Surface mounted set, Plaster Set, Safety Cable
Approval and Application	
Ingress protection code	IP20
Mech. impact protection code	-
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	4000 lm
Initial LED luminaire efficacy	100 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	> 80
Initial chromaticity	-
Initial input power	40 W



# **PILA LED Panel**

### Over Time Performance (IEC Compliant)

Lifetime L70

35,000 h


-

### **Application Conditions**

Performance ambient temperature Tq

Product Data	
Full product code	87195149599729900
Order product name	PILA RCOO7B LED4OS/840 PSU I W60L60 NOC
EAN/UPC - Product	871951495997299
Order code	911401879584
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401879584
Net Weight (Piece)	2.100 kg

### **Dimensional drawing**



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

### pila-led.com



# **PILA LED panel**

# PILA RC007B LED40S/840 PSU I W60L60 OC

PILA Panel - system flux 4000 lm - 840 neutral white

## **Benefits**

- Applicable for wide range of applications
- Supports energy saving
- Reliable quality



# **Product data**

#### General information

Lamp family code	LED40S [LED Module, system flux 4000 lm]
Light source color	840 neutral white
Light source replaceable	-
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Emergency Lighting	-
Optic type	-
Control interface	No
Connection	Fly wire
Protection class IEC	Safety class I
Mounting	-
CE mark	Yes
EU RoHS compliant	Yes
Constant light output	No
Number of products on MCB of 16 A type B	-
URG <19	Yes
Product family code	RC007C [PILA Panel]
Operating and Electrical	
Input Voltage	220-240 V
Input Frequency	50 to 60 Hz
Inrush current	-
Inrush time	-
Power Factor (Min)	> 0.9



Surge Protection (KV)	-
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Material	Steel
Optical cover/lens material	Polystyrene
Optical cover/lens finish	Micro prism
Overall diameter	595 mm
Overall height	595 mm
Overall height 1	34 mm
Color	White
Accesory	Suspension set, Surface mounted set, Plaster Set, Safety Cable
Approval and Application	
Ingress protection code	IP20
Mech. impact protection code	-
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	4000 lm
Initial LED luminaire efficacy	100 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	> 80
Initial chromaticity	-
Initial input power	40 W



# **PILA LED Panel**

### Over Time Performance (IEC Compliant)

Lifetime L70

35,000 h


-

### **Application Conditions**

Performance ambient temperature Tq

Product Data	
Full product code	87195149599899900
Order product name	PILA RCOO7B LED4OS/840 PSU I W60L60 OC
EAN/UPC - Product	871951495998999
Order code	911401879684
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401879684
Net Weight (Piece)	2.100 kg

### **Dimensional drawing**



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.