

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** PHILIPS

**Supplier's address:** Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

**Model identifier:** 8720169165793

## Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	E27		
Mains or non-mains:	MLS	Connected light source (CLS):	Yes
Colour-tuneable light source:	Yes	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Only with specific dimmers

## Product parameters

Parameter	Value	Parameter	Value
-----------	-------	-----------	-------

### General product parameters:

Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	7	Energy efficiency class	G
Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	470 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	2200...6500
On-mode power ( $P_{on}$ ), expressed in W	6,3	Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal	0,00
Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal	0,50	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	80
Outer dimensions without separate control gear, light-	Height	142	Spectral power distribution in the range 250 nm to 800 nm, at full-load
	Width	95	
	Depth	95	
			See image in last page

ing control parts and non-lighting control parts, if any (millimetre)			
Claim of equivalent power <sup>(a)</sup>	Yes	If yes, equivalent power (W)	40
		Chromaticity coordinates (x and y)	0,458 0,410
<b>Parameters for LED and OLED light sources:</b>			
R9 colour rendering index value	0	Survival factor	0,90
the lumen maintenance factor	0,93		
<b>Parameters for LED and OLED mains light sources:</b>			
displacement factor (cos $\phi_1$ )	0,00	Colour consistency in McAdam ellipses	6
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.	-(b)	If yes then replacement claim (W)	-
Flicker metric (Pst LM)	1,0	Stroboscopic effect metric (SVM)	0,4

(a): not applicable;

(b): not applicable;



Model placed on the Union market from 18/06/2024.



**EPREL registration number:** 1901107

<https://eprel.ec.europa.eu/qr/1901107>

**Supplier:** Signify Netherlands B.V. (Manufacturer)

**Website:** [www.signify.com](http://www.signify.com)

**Customer care service:**

**Name:** Customer Care Philips

**Website:** [www.philips.com/lighting](http://www.philips.com/lighting)

**Email:** [EPREL.PhilipsLighting@Signify.com](mailto:EPREL.PhilipsLighting@Signify.com)

**Phone:** 00800 744 547 75

**Address:**

I.B.R.S./C.C.R.I. /Numéro 10461  
5600VB Eindhoven  
Netherlands