

PHILIPS

Filament Candle
Clear 40W P45 E14

LED

2700K

470 lm

15000 h



8718699763152



Warm white light, no compromise on light quality

Familiar shapes you know and love. They use around 85% less energy than traditional light bulbs thanks to the latest LED energy-saving technology and last ten times longer.

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Create the right light for your home

- Perfect for decorative fixtures

High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Replaces lustre incandescents

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

Perfect for decorative fixtures



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips and post lights.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 8.2 cm
- Width: 4.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

Other characteristics

- Efficacy: 109 lm/W

Packaging information

- EAN: 8718699763152
- EOC: 871869976315201
- Product title: LED classic 40W
P45E14WW CL ND RFSRT4 UK

Power consumption

- Power factor: 0.41
- Voltage: 220–240 V
- Wattage: 4.3 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F

Product dimensions and weight

- Length: 8.2 cm

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 387409

Packaging dimensions and weight

- EAN/UPC – product: 8718699763152
- Net weight: 0.02 kg
- Gross weight: 0.04 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm
- Material number (12NC):
929001890406



Issue date: 2024-07-25
Version: 0.231

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com