

PHILIPS

Candle 7W T25 E14

LED

2700K

70 lm

15000 h



8718699771690



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Light beyond illumination

- For use in fridges and freezers

Highlights

Replaces lustre incandescents

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Special-purpose appliance bulb

Philips fridge bulbs can be used in fridges, freezers and similar places subject to low operating temperatures. Easily replace your appliance bulbs with a Philips fridge bulb for a long, useful life.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Type of glass: Frosted
- Dimmable: No
- Lamp Finish: Frosted
- Bulb material: Plastic

Lamp dimensions

- Height: 5.9 cm
- Width: 2.5 cm

Design and finishing

- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 70 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 827 | CCT of 2700K
- Correlated Colour Temperature: 2700 K
- Luminous Flux: 70 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 77.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 77 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699771690
- EOC: 871869977169000
- Product title: LED 7W T25 E14 WW FR ND 1SRT6

Power

- Power Factor (Fraction): 0.4

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 0.9 W
- Wattage equivalent: 7 W
- Power Consumption: 0.9 W
- Energy efficiency label (EEL): G

Product dimensions and weight

- Length: 5.9 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 406215
- Flux measurement reference: Sphere
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap base: E14

Packaging dimensions and weight

- EAN/UPC - product: 8718699771690
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm
- Material number (12NC): 929002401355



Issue date: 2024-07-25
Version: 0.84

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com