

PHILIPS

Filament Candle Clear
25W Filament P45 E14 x2

LED

2700K

250 lm

15000 h



8719514300323



Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Create the right light for your home

- Perfect for decorative fixtures

High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Similar shape and size as standard incandescent lamps



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs. Brad, review this copy again for all of these. Does not read well.

Perfect for decorative fixtures



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips and post lights.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 8 cm
- Width: 4.5 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 125 lm/W

Packaging information

- EAN: 8719514300323
- EOC: 871951430032300
- Product title: LED classic 25W P45 E14WWCLND 2SRT6

Power consumption

- Power factor: 0.41
- Voltage: 220–240 V
- Wattage: 2 W
- Wattage equivalent: 25 W
- Energy efficiency label (EEL): E

Product dimensions and weight

- Length: 8.2 cm

Technical specifications

- Frequency: 50–60 Hz
- EPREL Registration Number: 387363

Packaging dimensions and weight

- EAN/UPC – product: 8719514300323
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 11.5 cm



Issue date: 2025-03-11
Version: 0.292

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com