

PHILIPS

Capsule 25 W G9
G9 x2

LED

2700K

220 lm

15000 h



8720169302051



Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

- True incandescent-like warm white light

Choose for a sustainable solution

- Saves up to 80% energy

Create the right light for your home

- A simple LED for everyday use

Highlights

True incandescent-like warm white light



This bulb has a colour temperature of 2,700 K, providing you with a warm,

tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design.

Saves up to 80% energy



Enjoy the energy savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: G9
- Lamp Finish: Frosted
- Dimmable: No
- Bulb material: Plastic

Lamp dimensions

- Height: 4.3 cm
- Width: 1.4 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 320 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 220 lm

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 115 lm/W

Packaging information

- EAN: 8720169302051
- EOC: 872016930205100
- Product title: LED 25W G9 WW ND 2SRT6 UK

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage: 1.9 W
- Wattage equivalent: 25 W
- Energy efficiency label (EEL): E

Product dimensions and weight

- Length: 4.3 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1932582

Packaging dimensions and weight

- EAN/UPC - product: 8720169302051
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm



Issue date: 2025-03-20
Version: 0.144

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com