

PHILIPS

Filament Bulb Clear
60W A60 E27

LED

2200-2700K

806lm

15000h

Dimming



8719514323834



Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose for a sustainable solution

- Better for your wallet and your planet

Create the right light for your home

- Perfect for general room lighting

Highlights

Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Clear
- Dimmable: Only with specific dimmers
- Bulb Finish: Clear
- Bulb Material: Glass

Bulb dimensions

- Height: 10.4 cm
- Width: 6 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2200-2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: instant full light
- Color Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

Other characteristics

- Efficacy: 136 lm/W

Packaging information

- EAN: 8719514323834
- EOC: 871951432383400
- Product title: LED classic 60W A60 E27 CL WGD90 SRT4

Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 5.9 W
- Wattage equivalent: 60 W
- Energy Efficiency Label (EEL): D

Product dimensions and weight

- Length: 10.4 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1109131

8719514323834

Packaging dimensions and weight

- EAN/UPC - product: 8719514323834
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2024-11-21
Version: 0.431

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com