

PHILIPS

Candle 40W B35
E14

LED

2700K

470lm

15000h

220-240 V

8718696454916



Light that's easy on your eyes

Poor quality light could cause eye strain. It's more important than ever to properly light your home. Philips LED lamps fulfill stringent test criteria to ensure they meet our Eyecomfort requirements†

Sustainable choice

- Lasts up to 15 years
- Very low energy consumption; saving at least 80%

Create a warm atmosphere

- True incandescent-like warm white light (2700 K)

High quality light

- Designed for the comfort of your eyes
- No visible flicker

Instant light (LED)

- Instant light when switched on

Highlights

Lasts up to 15 years

With a lifetime of up to 15.000 hours, this Philips LED lamp will ensure your desired atmosphere for up to 15 years.*

Very low energy consumption



When you switch to a Philips LED light bulb, you immediately use up to 80% less energy without sacrificing light output and quality.

Warm white light (2700K)

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Instant light when switched on

No need to wait: Philips LED light bulbs provide their full level of brightness immediately upon switching on.

Specifications

Bulb characteristics

- Shape: Candle
- Lamp shape: Non directional candle
- Socket: E14
- Lamp shape code: B35
- Bulb Finish: Clear
- Dimmable: No
- Bulb Material: Plastic

Bulb dimensions

- Height: 10.6 cm
- Width: 3.5 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: instant full light

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 85 lm/W

Packaging information

- Product family: EyeComfort

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 5.5 W
- Wattage equivalent: 40 W

Product dimensions and weight

- Length: 10.6 cm

Technical specifications

- Frequency: 50–60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 8718696454916
- Net weight: 0.04 kg
- Gross weight: 0.05 kg
- Height: 14 cm
- Length: 4.5 cm
- Width: 4.5 cm



Issue date: 2025-03-18
Version: 0.754

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com