

PHILIPS

Recessed spot light

Functional

Slim Star

White

8719514272460



Durable and bright

Essential Spot light to create perfect ambience

Designed for your living- and bedroom

- Create a stylish and welcoming atmosphere

Match your interior

- Compact design

Light effect

- Bright and focused beam
- Available in Warm White, Cool White or Cool Daylight

Mounting

- Integrated driver with connector for easy installation.

Durability

- Long life span up to 15,000 hours

Highlights

Create a stylish atmosphere

This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define the localised ambience you have always desired.

Compact design

Compact size allows luminaire to be placed in small spaces.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Available in Warm White, Cool White or Cool Daylight

Different light colors can affect mood: warm white is perfect for relaxation, cool white for concentration and cool daylight for energizing you

Integrated driver with connector for easy installation.

Allows for safe and easy installation with no knowledge or wiring required.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Color: White
- Material: Plastic

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 30 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.055 kg
- Cut out length: 7.3 cm
- Cut out width: 7.3 cm
- Height: 4.5 cm
- Length: 8.8 cm
- Width: 8.8 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 88 mm
- Total lumen output fixture: 450
- Light color: 3000
- Mains power: 220–240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 5
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC – product: 8719514272460
- Net weight: 0.07 kg
- Gross weight: 0.1 kg
- Height: 5.5 cm
- Length: 10 cm
- Width: 10 cm
- Material number (12NC): 929001957317



Issue date: 2024-09-17
Version: 0.235

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com