

PHILIPS

Bell Switch

Switches & Sockets

Smart+

Matte Black

1 Module

10A

913713639101



Switch to a classy interior

Philips Smart+ Matt Black range adds premium décor to your wall with a mix blend of Glossy & Matt finish.

Easy to use

- Front insertion & front removal
- Low insert height

Safe to use

- FR Grade Polycarbonate Material
- ISI mark
- Safe to use even with wet hands
- Spark shield

Longer lifetime

- Brass terminals
- Brass screw
- Silver based contact rivet
- Superior material quality

Choose for a sustainable solution

- RoHS compliant

Highlights

Front insertion & front removal

Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

Low insert height

Low insert height so that you get more space for wiring inside the installed box.

FR Grade Polycarbonate Material

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

ISI mark

ISI mark (tested as per indian standard IS3854).

Safe to use even with wet hands

No seepage of water due to precision & covered design.

Spark shield

No visible spark during the switch operation.

Brass terminals

Brass terminal for connection for longer, uninterrupted life.

Brass screw

Brass screw for longer, carefree operations.

Silver based contact rivet

Silver based contact rivet for better connectivity and long life.

Superior material quality

Phosphorus bronze internal wire which last long and makes the product long lasting.

RoHS compliant

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

Specifications

Design and finishing

- Color: Black
- Material: Metal, Plastic
- Module/Gang: 1 Module
- Product Range: Smart+
- Minimum Installation Box Depth: 50 mm

Durability

- Number of Operation Cycles: 40,000

Interactivity

- Current (A): 10

Miscellaneous

- Approval Marks: BIS Certificate

Other characteristics

- Installation Type: Screwed Installation
- Indicator Type: No Indicator

Power

- Electrical Load Type: Resistive load

Power consumption

- Voltage: 240 V

Product dimensions and weight

- Length: 5 cm
- Width: 2.25 cm
- Depth: 3.35 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718696664544
- Net weight: 0.02 kg
- Gross weight: 0.02 kg
- Height: 3.4 cm
- Length: 5 cm
- Width: 2.3 cm
- Material number (12NC): 913713639101



Issue date: 2024-06-15
Version: 0.272

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com