

PHILIPS

2/3 Pin socket

Switches & Sockets

Smart Antibacterial

White

2 Module

6A

913713822201



Ensure a safer living with Smart Anti- bacterial Range

Philips Antibacterial Range kills 99% germs with in-built Silver Ion Technology.

Easy to use

- Shrouded terminals with captive screws
- Front insertion & front removal
- Glossy finish
- Low insert height
- Convenient grip for plug

Safe to use

- FR Grade Polycarbonate Material
- Safe to use even with wet hands

Longer lifetime

- Brass terminals
- Brass screw

Advanced

- Silver Ion Technology
- BactiSafe
- Non Toxic life long

913713822201

Choose for a sustainable solution

- RoHS compliant

Highlights

Shrouded terminals with captive screws

Shrouded terminals for easy installation. Screws won't come out during wire fixing.

Front insertion & front removal

Smart way to preserve your designer walls, remove your switch/socket without dismantling the plates. Inserts can be fixed or removed from front.

Glossy finish

Glossy external finish for easy to clean and long lasting finish.

Low insert height

Low insert height so that you get more space for wiring inside the installed box.

Convenient grip for plug

Convenient gripping inside the socket for the inserted plug for better connectivity.

FR Grade Polycarbonate Material

Best quality polycarbonate material which doesn't catch fire easily. Material also clears the Glow Wire Test @ 850 Degree Celsius.

Safe to use even with wet hands

No seepage of water due to precision & covered design.

Brass terminals

Brass terminal for connection for longer, uninterrupted life.

Brass screw

Brass screw for longer, carefree operations.

Silver Ion Technology

Material has Silver Ions which turn bacteria into deadly zombies.

BactiSafe

Kills 99% bacteria as per test protocol JIS Z 2801:2010 conducted on E. Coli & Staphylococcus.

Non Toxic life long

Silver Ion technology has longer life of more than 10 years as it's built in material & has no side effects.

RoHS compliant

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

Specifications

Design and finishing

- Color: White
- Material: PC
- Module/Gang: 2 Module
- Socket/connector Type: 2 Pin + E
- Product Range: Smart Antibacterial
- Minimum Installation Box Depth: 50 mm

Durability

- Number of Operation Cycles: 5,000

Interactivity

- Current (A): 6A

Other characteristics

- Installation Type: Fast Installation
- Indicator Type: No Indicator

Power

- Electrical Load Type: Resistive load

Power consumption

- Voltage: 240 V

Product dimensions and weight

- Length: 5 cm
- Width: 4.5 cm
- Depth: 3.53 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699738075
- Net weight: 0.03 kg
- Gross weight: 0.03 kg
- Height: 3.5 cm
- Length: 5 cm
- Width: 4.5 cm



Issue date: 2025-03-22
Version: 0.339

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com