



Philips GentleSpace – High-quality, efficient lighting engineered for excellence in tough environments

GentleSpace gen4

GentleSpace gen4 is the ultimate lighting solution for industrial settings and indoor sports facilities. It exceeds expectations by ensuring superior light quality, improving employee safety and productivity, and complying with all the relevant safety regulations. Engineered for longevity, GentleSpace gen4 reduces the frequency, hassle, and costs of maintenance, making it ideal for high-ceiling installations. Its energy-efficient design cuts operational expenses, offering maximum application efficiency and an attractive total cost of ownership (TCO). This product range offers a wide variety of optics, beam angles (from very narrow to wide), lumen packages, and connectivity options. With GentleSpace gen4 you can easily create a tailor-made lighting solution for every high-ceiling application. Its modern, flat design makes it easier to install, clean, and maintain. The single optical window design provides superior visual performance. A variety of mounting possibilities and connectors, like the pre-mounted IP65 connector, enable quick and easy installation. The robust design allows to withstand harsh conditions in all sorts of environments. You can choose between various cover materials, including specialized variants for extreme temperatures (XT), hazardous areas (ATEX 2/22), and sports applications. Additionally, GentleSpace gen4 offers advanced connectivity options. It's ready to use in connected lighting systems like Interact. Reliable, high-efficiency lighting with smart connectivity – a bright choice for a better future. Embrace sustainability with GentleSpace gen4, the highbay lighting solution that complies with the principles of the circular economy by prioritizing durability and recyclability. The luminaire is serviceable, with all the information available at your fingertips via the Signify Service tag app. Whether you are looking

GentleSpace gen4

for a reliable “fit and forget” solution or one that can be adapted and controlled after installation, GentleSpace gen4 is the right choice for you.

Benefits

- Robust design, created to withstand harsh conditions in all sorts of environments
- Compact product architecture, resistant to high impact (IK08), water, and dust (IP65)
- Excellent light uniformity and low glare for optimized working conditions with improved safety and greater visual comfort
- Attractive total cost of ownership thanks to its high luminous efficacy (up to 189 lm/W), long lifetime (100,000 hours @L85), and optimized lighting plan that requires fewer luminaires per application
- Easy installation. Single-piece, lighter architecture (approximately 20% lighter than the previous generation) with multiple mounting options for flexible installation in various environments and conditions
- Interact Ready connectivity for smart lighting. Connect to the cloud and discover additional ways to save energy through optimized efficiency, motion sensing and daylight harvesting, as well as improved lighting management, productivity, and safety
- Engineered with sustainability in mind. Meets lighting for circularity criteria to help you achieve your sustainability goals

Features

- Exceptional performance with UltraEfficient (UE, 189 lm/W) and High-Efficiency (HE, 183 lm/W) versions
- Long service life of 100,000 hours at L85
- High water (IP65) and impact protection (IK08)
- Wide variety of optics (wide beam/medium beam/narrow beam/extra narrow beam/high-rack/asymmetrical)
- Special options for a broad range of applications: Extreme version (XT) up to 70°C, Safety Class I or II, swimming pool protected version (SWP), marine protection (MSP), VDE certified ball-proof (BP) option, ATEX 2/22 certified version. Tested against a broad list of chemical substances that may be present in industrial settings
- Detachable mounting system for easy installation, including various mounting options and connectors (IP65 pre-mounted connector, or fly-wire cable)
- Robust, die-cast aluminum housing with efficient thermal management and flat front and rear design for easy installation, cleaning, and maintenance
- Single LED module design for superior light quality
- Access to the Signify Service tag app with service and maintenance information

Application

- Manufacturing sites (from food and beverage to heavy industry)
- Warehouses and logistics centers
- Indoor sports facilities, swimming pools, and exhibition halls


Versions



GentleSpace gen4-small, bracket,
Interact ready


Dimensional drawing

BY580X suspended




With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

700s suspended




With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

BY581X suspended




With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

BY580P, BY582P suspended




With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m

BY581P, BY583P Bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m


BY580P, BY582P Bracket



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m, or 2m


Dimensional drawing

BY581X Bracket




With Wieland connector on a cable or free cable finish, cable length is 0.5m or 1m or 1.5m, or 2m

BY580X Bracket




With Wieland connector on a cable or free cable finish, cable length is 0.5m or 1m or 1.5m, or 2m

7005 Bracket




With Wieland connector on a cable or free cable finish, cable length is 0.5m or 1m or 1.5m, or 2m

BY581P, BY583P suspended




With Wieland connector on a cable or free cable finish, cable length is 0.5m or 1m or 1.5m, or 2m

Product details



GentleSpace gen4-large, suspension



GentleSpace gen4-small, suspension

General Information

| | |
|----------------------|--------|
| Driver included | Yes |
| Number of gear units | 1 unit |

Light Technical

| | |
|------------|-------------|
| Optic type | Symmetrical |
|------------|-------------|

Operating and Electrical

| | |
|----------------------|----------------|
| Protection class IEC | Safety class I |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |

Mechanical and Housing

| | |
|-------------------------|--------|
| Housing Color | Silver |
| Ingress protection code | IP65 |

Emergency Operation

| | |
|-------------------|----|
| Central Emergency | No |
|-------------------|----|

Approval and Application

| | |
|-------------------|---|
| CE mark | Yes |
| ENEC mark | ENEC mark |
| Flammability mark | For mounting on easily flammable surfaces |

Initial Performance (IEC Compliant)

| | |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

General Information

| Order Code | Full Product Name | Service tag |
|--------------|---|-------------|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | Yes |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | Yes |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | Yes |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | Yes |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | Yes |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | Yes |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | Yes |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | Yes |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | Yes |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | Yes |
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | Yes |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | Yes |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | Yes |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | Yes |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | Yes |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | Yes |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | Yes |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | Yes |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | Yes |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | Yes |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | Yes |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | Yes |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | Yes |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | Yes |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | Yes |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | Yes |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | Yes |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | Yes |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | Yes |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | Yes |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | Yes |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | Yes |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | Yes |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | Yes |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | Yes |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | Yes |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | - |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | - |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | Yes |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | Yes |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | Yes |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | Yes |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | Yes |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | Yes |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | Yes |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | - |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | - |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | Yes |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | Yes |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | - |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | - |

| Order Code | Full Product Name | Service tag |
|--------------|--|-------------|
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | Yes |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | Yes |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | - |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | - |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | Yes |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | Yes |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | - |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | Yes |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | Yes |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | Yes |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | Yes |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | Yes |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | Yes |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | Yes |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | Yes |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | Yes |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | Yes |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | Yes |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | Yes |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | Yes |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | Yes |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | - |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | - |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | Yes |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | Yes |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | Yes |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | Yes |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | Yes |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | Yes |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | Yes |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | - |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | - |

Light Technical (1/2)

| Order Code | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|--|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | - | 4000 K | >80 | 167 lm/W |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | - | 4000 K | >80 | 177 lm/W |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | - | 4000 K | >80 | 167 lm/W |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | - | 4000 K | >80 | 177 lm/W |

| Order Code | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|--|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | - | 4000 K | >80 | 174 lm/W |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | - | 4000 K | >80 | 184 lm/W |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | - | 4000 K | >80 | 171 lm/W |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | - | 4000 K | >80 | 167 lm/W |

GentleSpace gen4

| Order Code | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|--|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | - | 4000 K | >80 | 174 lm/W |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | - | 4000 K | >80 | 167 lm/W |
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | - | 4000 K | >80 | 178 lm/W |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | - | 4000 K | >80 | 175 lm/W |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | - | 4000 K | >80 | 184 lm/W |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | - | 4000 K | >80 | 177 lm/W |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | - | 4000 K | >80 | 174 lm/W |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | - | 4000 K | >80 | 174 lm/W |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | - | 4000 K | >80 | 184 lm/W |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | - | 4000 K | >80 | 184 lm/W |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | - | 4000 K | >80 | 167 lm/W |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | - | 4000 K | >80 | 175 lm/W |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | - | 4000 K | >80 | 167 lm/W |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | - | 4000 K | >80 | 175 lm/W |

| Order Code | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 910505102878 | BY580P 130S/840 DIA WB GC SI | - | 4000 K | >80 | 171 lm/W |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | - | 4000 K | >80 | 167 lm/W |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | - | 4000 K | >80 | 178 lm/W |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | - | 4000 K | >80 | 175 lm/W |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | - | 4000 K | >80 | 155 lm/W |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | - | 4000 K | >80 | 164 lm/W |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | - | 4000 K | >80 | 167 lm/W |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | - | 4000 K | >80 | 175 lm/W |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | - | 4000 K | >80 | 169 lm/W |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | - | 4000 K | >80 | 164 lm/W |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | - | 4000 K | >80 | 178 lm/W |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | - | 4000 K | >80 | 174 lm/W |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | 10 or 24 degree(s) | 4000 K | >80 | 164 lm/W |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | 10 or 24 degree(s) | 4000 K | >80 | 174 lm/W |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | - | 4000 K | >80 | 164 lm/W |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | - | 4000 K | >80 | 174 lm/W |

GentleSpace gen4

| Order Code | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | - | 4000 K | >80 | 164 lm/W |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | - | 4000 K | >80 | 174 lm/W |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | - | 6500 K | >80 | 164 lm/W |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | - | 6500 K | >80 | 172 lm/W |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | - | 3000 K | >80 | 155 lm/W |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | - | 3000 K | >80 | 159 lm/W |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | - | 4000 K | >90 | 157 lm/W |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | - | 4000 K | >80 | 167 lm/W |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | - | 4000 K | >80 | 175 lm/W |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | - | 4000 K | >80 | 167 lm/W |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | - | 4000 K | >80 | 175 lm/W |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | - | 4000 K | >80 | 167 lm/W |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | - | 4000 K | >80 | 175 lm/W |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | - | 4000 K | >80 | 174 lm/W |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | - | 4000 K | >80 | 181 lm/W |

| Order Code | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | - | 4000 K | >80 | 174 lm/W |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | - | 4000 K | >80 | 181 lm/W |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | - | 4000 K | >80 | 174 lm/W |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | - | 4000 K | >80 | 184 lm/W |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | - | 4000 K | >80 | 189 lm/W |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | - | 4000 K | >80 | 174 lm/W |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | - | 4000 K | >80 | 167 lm/W |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | - | 4000 K | >80 | 181 lm/W |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | - | 4000 K | >80 | 177 lm/W |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | - | 4000 K | >80 | 162 lm/W |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | - | 4000 K | >80 | 171 lm/W |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | - | 4000 K | >80 | 174 lm/W |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | - | 4000 K | >80 | 181 lm/W |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | - | 4000 K | >80 | 171 lm/W |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | - | 4000 K | >80 | 167 lm/W |

GentleSpace gen4

| Order Code | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|--|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | - | 4000 K | >80 | 181 lm/W |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | - | 4000 K | >80 | 175 lm/W |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | 10 or 24 degree(s) | 4000 K | >80 | 171 lm/W |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | 10 or 24 degree(s) | 4000 K | >80 | 181 lm/W |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | - | 4000 K | >80 | 171 lm/W |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | - | 4000 K | >80 | 181 lm/W |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | - | 4000 K | >80 | 171 lm/W |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | - | 4000 K | >80 | 181 lm/W |

| Order Code | Full Product Name | Beam angle of light source | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) |
|--------------|---|----------------------------|------------------------------------|-----------------------------|---------------------------------|
| 910505102927 | BY581P 250S/865 DIA WB GC SI | - | 6500 K | >80 | 171 lm/W |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | - | 6500 K | >80 | 179 lm/W |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | - | 3000 K | >80 | 162 lm/W |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | - | 3000 K | >80 | 171 lm/W |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | - | 4000 K | >90 | 165 lm/W |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | - | 4000 K | >80 | 174 lm/W |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | - | 4000 K | >80 | 181 lm/W |

Light Technical (2/2)

| Order Code | Full Product Name | Luminous Flux |
|--------------|---|---------------|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | 70,000 lm |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | 70,000 lm |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | 70,000 lm |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | 70,000 lm |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | 25,000 lm |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | 25,000 lm |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | 13,000 lm |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | 17,000 lm |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | 25,000 lm |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | 35,000 lm |
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | 13,000 lm |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | 17,000 lm |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | 25,000 lm |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | 35,000 lm |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | 25,000 lm |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | 25,000 lm |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | 25,000 lm |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | 25,000 lm |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | 17,000 lm |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | 17,000 lm |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | 17,000 lm |

| Order Code | Full Product Name | Luminous Flux |
|--------------|--------------------------------------|---------------|
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | 17,000 lm |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | 13,000 lm |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | 17,000 lm |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | 13,000 lm |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | 17,000 lm |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | 17,000 lm |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | 17,000 lm |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | 17,000 lm |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | 17,000 lm |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | 13,000 lm |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | 17,000 lm |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | 13,000 lm |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | 17,000 lm |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | 17,000 lm |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | 17,000 lm |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | 17,000 lm |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | 17,000 lm |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | 17,000 lm |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | 17,000 lm |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | 17,000 lm |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | 17,000 lm |

| Order Code | Full Product Name | Luminous Flux |
|--------------|--|---------------|
| 910505102930 | BY580P 170S/830 DIA WB GC SI | 17,000 lm |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | 17,000 lm |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | 17,000 lm |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | 17,000 lm |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | 17,000 lm |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | 17,000 lm |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | 17,000 lm |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | 17,000 lm |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | 17,000 lm |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | 25,000 lm |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | 25,000 lm |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | 25,000 lm |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | 25,000 lm |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | 25,000 lm |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | 25,000 lm |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | 20,000 lm |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | 25,000 lm |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | 35,000 lm |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | 25,000 lm |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | 35,000 lm |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | 25,000 lm |

| Order Code | Full Product Name | Luminous Flux |
|--------------|--|---------------|
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | 25,000 lm |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | 25,000 lm |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | 25,000 lm |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | 25,000 lm |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | 35,000 lm |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | 25,000 lm |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | 35,000 lm |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | 25,000 lm |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | 25,000 lm |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | 25,000 lm |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | 25,000 lm |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | 25,000 lm |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | 25,000 lm |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | 25,000 lm |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | 25,000 lm |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | 25,000 lm |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | 25,000 lm |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | 25,000 lm |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | 25,000 lm |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | 25,000 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|--------------|---------------------------------------|-------------------|--|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | 420 W | No |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | 397 W | No |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | 420 W | No |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | 397 W | No |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | 144 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | 136 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | 76 W | Yes (relates to presence/movement detection and daylight harvesting) |

| Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|--------------|------------------------------------|-------------------|--|
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | 102 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | 144 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | 210 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | 73 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | 97 W | Yes (relates to presence/ |

| Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|--------------|---|-------------------|--|
| | | | movement detection and daylight harvesting) |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | 136 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | 198 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | 144 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | 144 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | 136 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | 136 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | 102 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | 97 W | Yes (relates to presence/movement detection and |

| Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|--------------|--------------------------------------|-------------------|-------------------------------|
| | | | daylight harvesting) |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | 102 W | No |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | 97 W | No |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | 76 W | No |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | 102 W | No |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | 73 W | No |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | 97 W | No |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | 110 W | No |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | 104 W | No |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | 102 W | No |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | 97 W | No |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | 77 W | No |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | 104 W | No |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | 73 W | No |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | 98 W | No |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | 104 W | No |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | 98 W | No |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | 104 W | No |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | 98 W | No |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | 104 W | No |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | 98 W | No |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | 104 W | No |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | 99 W | No |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | 110 W | No |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | 104 W | No |

| Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|--------------|--|-------------------|-------------------------------|
| 910505102934 | BY580P 170S/940 DIA WB GC SI | 108 W | No |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | 102 W | No |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | 97 W | No |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | 102 W | No |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | 97 W | No |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | 102 W | No |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | 97 W | No |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | 144 W | No |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | 138 W | No |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | 144 W | No |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | 138 W | No |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | 144 W | No |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | 136 W | No |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | 106 W | No |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | 144 W | No |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | 210 W | No |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | 138 W | No |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | 198 W | No |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | 154 W | No |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | 146 W | No |

| Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|--------------|--|-------------------|-------------------------------|
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | 144 W | No |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | 138 W | No |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | 146 W | No |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | 210 W | No |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | 138 W | No |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | 200 W | No |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | 146 W | No |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | 138 W | No |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | 146 W | No |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | 138 W | No |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | 146 W | No |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | 138 W | No |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | 146 W | No |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | 140 W | No |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | 154 W | No |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | 146 W | No |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | 152 W | No |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | 144 W | No |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | 138 W | No |

Controls and Dimming

| Order Code | Full Product Name | Dimmable | Embedded control | Maximum dim level |
|--------------|---------------------------------|----------|------------------|-------------------|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | Yes | - | 10% |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | Yes | - | 10% |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | Yes | - | 10% |

| Order Code | Full Product Name | Dimmable | Embedded control | Maximum dim level |
|--------------|---------------------------------------|----------|--------------------|-------------------|
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | Yes | - | 10% |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | Yes | Sensor SNH (R) 210 | - |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | Yes | Sensor SNH (R) 210 | - |

GentleSpace gen4

| Order Code | Full Product Name | Dimmable | Embedded control | Maximum dim level |
|--------------|---|----------|--------------------|-------------------|
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | Yes | Sensor SNH (R) 210 | - |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | Yes | Sensor SNH (R) 210 | - |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | Yes | Sensor SNH (R) 210 | - |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | No | - | - |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | No | - | - |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | Yes | - | 10% |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | Yes | - | 10% |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | Yes | - | 10% |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | Yes | - | 10% |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | Yes | - | 10% |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | Yes | - | 10% |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | Yes | - | 10% |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | Yes | - | 10% |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | Yes | - | 10% |

| Order Code | Full Product Name | Dimmable | Embedded control | Maximum dim level |
|--------------|--|----------|------------------|-------------------|
| 910505102899 | BY580P 170S/840 DIA MB GC SI | Yes | - | 10% |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | Yes | - | 10% |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | Yes | - | 10% |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | Yes | - | 10% |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | Yes | - | 10% |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | Yes | - | 10% |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | Yes | - | 10% |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | Yes | - | 10% |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | Yes | - | 10% |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | Yes | - | 10% |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | Yes | - | 10% |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | Yes | - | 10% |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | Yes | - | 10% |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | Yes | - | 10% |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | Yes | - | 10% |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | Yes | - | 10% |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | Yes | - | 10% |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | Yes | - | 10% |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | Yes | - | 10% |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | Yes | - | 10% |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | Yes | - | 10% |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | Yes | - | 10% |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | Yes | - | 10% |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | Yes | - | 10% |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | No | - | - |

| Order Code | Full Product Name | Dimmable | Embedded control | Maximum dim level |
|--------------|--------------------------------------|----------|------------------|-------------------|
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | No | - | - |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | Yes | - | 10% |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | Yes | - | 10% |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | Yes | - | 10% |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | Yes | - | 10% |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | Yes | - | 10% |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | Yes | - | 10% |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | Yes | - | 10% |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | Yes | - | 10% |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | Yes | - | 10% |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | Yes | - | 10% |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | Yes | - | 10% |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | Yes | - | 10% |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | Yes | - | 10% |

| Order Code | Full Product Name | Dimmable | Embedded control | Maximum dim level |
|--------------|--|----------|------------------|-------------------|
| 910505102915 | BY581P 250S/840 DIA NB GC SI | Yes | - | 10% |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | Yes | - | 10% |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | Yes | - | 10% |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | Yes | - | 10% |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | Yes | - | 10% |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | Yes | - | 10% |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | Yes | - | 10% |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | Yes | - | 10% |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | Yes | - | 10% |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | Yes | - | 10% |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | Yes | - | 10% |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | Yes | - | 10% |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | Yes | - | 10% |

Mechanical and Housing

| Order Code | Full Product Name | Mech. impact protection code |
|--------------|---|------------------------------|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | IK07 |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | IK07 |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | IK07 |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | IK07 |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | IK03 |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | IK03 |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | IK03 |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | IK03 |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | IK03 |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | IK03 |
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | IK03 |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | IK03 |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | IK03 |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | IK03 |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | IK03 |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | IK03 |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | IK03 |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | IK03 |

| Order Code | Full Product Name | Mech. impact protection code |
|--------------|---------------------------------------|------------------------------|
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | IK03 |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | IK03 |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | IK07 |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | IK07 |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | IK07 |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | IK07 |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | IK07 |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | IK07 |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | IK07 |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | IK07 |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | IK07 |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | IK07 |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | IK07 |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | IK07 |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | IK07 |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | IK07 |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | IK07 |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | IK07 |

| Order Code | Full Product Name | Mech. impact protection code |
|--------------|--|------------------------------|
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | IK07 |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | IK07 |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | IK07 |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | IK07 |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | IK07 |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | IK07 |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | IK07 |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | IK07 |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | IK07 |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | IK07 |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | IK07 |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | IK07 |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | IK07 |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | IK07 |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | IK07 |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | IK07 |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | IK07 |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | IK07 |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | IK07 |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | IK07 |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | IK07 |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | IK07 |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | IK07 |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | IK07 |

| Order Code | Full Product Name | Mech. impact protection code |
|--------------|--|------------------------------|
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | IK07 |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | IK07 |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | IK07 |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | IK07 |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | IK07 |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | IK07 |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | IK07 |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | IK07 |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | IK07 |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | IK07 |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | IK07 |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | IK07 |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | IK07 |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | IK07 |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | IK07 |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | IK07 |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | IK07 |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | IK07 |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | IK07 |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | IK07 |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | IK07 |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | IK07 |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | IK07 |

Emergency Operation (1/2)

| Order Code | Full Product Name | Emergency lighting | Emergency flux | Type of emergency lighting battery | Power consumption during Central DC emergency mode |
|--------------|------------------------------------|--------------------|----------------|------------------------------------|--|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | - | - | - | - |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | - | - | - | - |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | - | - | - | - |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | - | - | - | - |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | - | - | - | - |

| Order Code | Full Product Name | Emergency lighting | Emergency flux | Type of emergency lighting battery | Power consumption during Central DC emergency mode |
|--------------|---------------------------------------|--------------------|----------------|------------------------------------|--|
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | - | - | - | - |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | - | - | - | - |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | - | - | - | - |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | - | - | - | - |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | - | - | - | - |
| 910505102860 | BY580X 130S/840 SIA | - | - | - | - |

| Order Code | Full Product Name | Emergency lighting | Emergency flux | Type of emergency lighting battery | Power consumption during Central DC emergency mode |
|--------------|--|---|----------------|------------------------------------|--|
| 910505102861 | HE WB GC SI H4 BY580X 170S/840 SIA | - | - | - | - |
| 910505102862 | HE WB GC SI H4 BY581X 250S/840 SIA | - | - | - | - |
| 910505102863 | HE WB GC SI H4 BY581X 350S/840 SIA | - | - | - | - |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | Emergency lighting 3 hours duration Pro version | 850 lm | Lithium | 5 W |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | Emergency lighting 3 hours duration with Wireless Interface | 850 lm | Lithium | 5 W |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | Emergency lighting 3 hours duration Pro version | 850 lm | Lithium | 5 W |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | Emergency lighting 3 hours duration with Wireless Interface | 850 lm | Lithium | 5 W |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | - | - | - | - |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | - | - | - | - |

| Order Code | Full Product Name | Emergency lighting | Emergency flux | Type of emergency lighting battery | Power consumption during Central DC emergency mode |
|--------------|---|---|----------------|------------------------------------|--|
| 910505102872 | BY580P 170S/840 PSU WB GC SI | - | - | - | - |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | - | - | - | - |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | - | - | - | - |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | - | - | - | - |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | - | - | - | - |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | - | - | - | - |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | - | - | - | - |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | - | - | - | - |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | Emergency lighting 3 hours duration Pro version | 450 lm | Lithium | 3 W |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | Emergency lighting 3 hours duration Pro version | 450 lm | Lithium | 3 W |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | - | - | - | - |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | - | - | - | - |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | - | - | - | - |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | - | - | - | - |

| Order Code | Full Product Name | Emergency lighting | Emergency flux | Type of emergency lighting battery | Power consumption during Central DC emergency mode |
|--------------|---|--------------------|----------------|------------------------------------|--|
| 910505102914 | BY580P 170S/840 DIA NB GC SI | - | - | - | - |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | - | - | - | - |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | - | - | - | - |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | - | - | - | - |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | - | - | - | - |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | - | - | - | - |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | - | - | - | - |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | - | - | - | - |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | - | - | - | - |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | - | - | - | - |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | - | - | - | - |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | - | - | - | - |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | - | - | - | - |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | - | - | - | - |
| 910505102892 | BY580P 170S/840 DIA | - | - | - | - |

| Order Code | Full Product Name | Emergency lighting | Emergency flux | Type of emergency lighting battery | Power consumption during Central DC emergency mode |
|--------------|---|--------------------|----------------|------------------------------------|--|
| | HE WB GC SI BR | | | | |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | - | - | - | - |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | - | - | - | - |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | - | - | - | - |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | - | - | - | - |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | - | - | - | - |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | - | - | - | - |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | - | - | - | - |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | - | - | - | - |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | - | - | - | - |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | - | - | - | - |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | - | - | - | - |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | - | - | - | - |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | - | - | - | - |

| Order Code | Full Product Name | Emergency lighting | Emergency flux | Type of emergency lighting battery | Power consumption during Central DC emergency mode |
|--------------|---|---|----------------|------------------------------------|--|
| 910505102887 | BY581P 250S/840 DIA WB PC SI | - | - | - | - |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | - | - | - | - |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | Emergency lighting 3 hours duration with DALI interface | 850 lm | Lithium | 5 W |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | Emergency lighting 3 hours duration with DALI interface | 850 lm | Lithium | 5 W |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | - | - | - | - |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | - | - | - | - |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | - | - | - | - |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | - | - | - | - |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | - | - | - | - |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | - | - | - | - |

| Order Code | Full Product Name | Emergency lighting | Emergency flux | Type of emergency lighting battery | Power consumption during Central DC emergency mode |
|--------------|---|--------------------|----------------|------------------------------------|--|
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | - | - | - | - |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | - | - | - | - |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | - | - | - | - |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | - | - | - | - |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | - | - | - | - |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | - | - | - | - |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | - | - | - | - |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | - | - | - | - |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | - | - | - | - |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | - | - | - | - |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | - | - | - | - |

Emergency Operation (2/2)

| Order Code | Full Product Name | Rated duration of the emergency lighting (when fully charged) |
|--------------|------------------------------------|---|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | - |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | - |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | - |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | - |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | - |

| Order Code | Full Product Name | Rated duration of the emergency lighting (when fully charged) |
|--------------|---------------------------------------|---|
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | - |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | - |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | - |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | - |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | - |

| Order Code | Full Product Name | Rated duration of the emergency lighting (when fully charged) |
|--------------|---|---|
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | - |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | - |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | - |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | - |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | 3 hour(s) |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | 3 hour(s) |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | 3 hour(s) |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | 3 hour(s) |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | - |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | - |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | - |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | - |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | - |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | - |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | - |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | - |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | - |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | - |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | 3 hour(s) |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | 3 hour(s) |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | - |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | - |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | - |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | - |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | - |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | - |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | - |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | - |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | - |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | - |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | - |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | - |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | - |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | - |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | - |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | - |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | - |

| Order Code | Full Product Name | Rated duration of the emergency lighting (when fully charged) |
|--------------|--|---|
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | - |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | - |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | - |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | - |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | - |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | - |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | - |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | - |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | - |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | - |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | - |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | - |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | - |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | - |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | - |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | - |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | - |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | 3 hour(s) |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | 3 hour(s) |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | - |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | - |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | - |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | - |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | - |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | - |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | - |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | - |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | - |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | - |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | - |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | - |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | - |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | - |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | - |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | - |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | - |

Approval and Application

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 (SVM) | |
|--------------|-------------------|---------------------------|-----------------------------------|---|--|
| | | | | Stroboscopic effect visibility measure | Stroboscopic effect visibility measure |
| 910505102953 | BY581P 700S/840 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.22 | 0.01 |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 (SVM) | |
|------------|-------------------|---------------------------|----------------|---|--|
| | | | | Stroboscopic effect visibility measure | Stroboscopic effect visibility measure |
| | DIA WB GC SI | | | | |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | Stroboscopic effect visibility measure (SVM) |
|--------------|---|---------------------------|---|---|--|
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.22 | 0.01 |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.22 | 0.01 |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.22 | 0.01 |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | Stroboscopic effect visibility measure (SVM) |
|--------------|---|---------------------------|---|---|--|
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | 0 °C to 25 °C | Temperature 850 °C, duration 30 s | 1 | 0.4 |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | 0 °C to 25 °C | Temperature 850 °C, duration 30 s | 1 | 0.4 |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | 0 °C to 25 °C | Temperature 850 °C, duration 30 s | 1 | 0.4 |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | 0 °C to 25 °C | Temperature 850 °C, duration 30 s | 1 | 0.4 |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 1 | 0.4 |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.04 | 0.07 |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.04 | 0.07 |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 (SVM) | |
|--------------|---|---------------------------|---|---|------|
| | | | | Stroboscopic effect visibility measure | |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | 0 °C to 25 °C | Temperature 850 °C, duration 30 s | 0.12 | 0.07 |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | 0 °C to 25 °C | Temperature 850 °C, duration 30 s | - | - |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 (SVM) | |
|--------------|---|---------------------------|---|---|------|
| | | | | Stroboscopic effect visibility measure | |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | Stroboscopic effect visibility measure (SVM) |
|--------------|--|---------------------------|---|---|--|
| 910505102934 | BY580P 170S/940 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | - | - |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505104547 | BY581P 250S/840 DIA HE WB | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | Stroboscopic effect visibility measure (SVM) |
|--------------|--|---------------------------|---|---|--|
| | GC SI SWP BR | | | | |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.04 | 0.07 |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.04 | 0.07 |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.22 | 0.01 |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.22 | 0.01 |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | 0 °C to 25 °C | Temperature 850 °C, duration 30 s | 0.12 | 0.07 |
| 910505102897 | BY581P 250S/840 DIA HE WB | 0 °C to 25 °C | Temperature 850 °C, duration 30 s | 0.12 | 0.07 |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | Stroboscopic effect visibility measure (SVM) |
|--------------|---|---------------------------|---|---|--|
| | GC SI ELD3 | | | | |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.22 | 0.01 |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.22 | 0.01 |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |

| Order Code | Full Product Name | Ambient temperature range | Glow-wire test | Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | Stroboscopic effect visibility measure (SVM) |
|--------------|--|---------------------------|---|---|--|
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | -30 to +55 °C | Temperature 650 °C, duration 30 s | 0.12 | 0.07 |

Initial Performance (IEC Compliant)

| Order Code | Full Product Name | Initial chromaticity |
|--------------|------------------------------------|-----------------------|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | (0.380, 0.375) SDCM 3 |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | (0.383, 0.377) SDCM 3 |

| Order Code | Full Product Name | Initial chromaticity |
|--------------|---------------------------------------|-----------------------|
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | (0.380, 0.375) SDCM 3 |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | (0.383, 0.377) SDCM 3 |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | (0.380, 0.375) SDCM 3 |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | (0.380, 0.375) SDCM 3 |

| Order Code | Full Product Name | Initial chromaticity |
|--------------|---|-----------------------|
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | (0.380, 0.375) SDCM 3 |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | (0.380, 0.375) SDCM 3 |
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | (0.383, 0.377) SDCM 3 |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | (0.383, 0.377) SDCM 3 |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | (0.383, 0.377) SDCM 3 |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | (0.383, 0.377) SDCM 3 |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | (0.380, 0.375) SDCM 3 |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | (0.380, 0.375) SDCM 3 |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | (0.383, 0.377) SDCM 3 |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | (0.383, 0.377) SDCM 3 |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | (0.380, 0.375) SDCM 3 |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | (0.383, 0.377) SDCM 3 |
| 910505102872 | BY580P 170S/840 PSU WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | (0.380, 0.375) SDCM 3 |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | (0.383, 0.377) SDCM 3 |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | (0.380, 0.375) SDCM 3 |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | (0.383, 0.377) SDCM 3 |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | (0.380, 0.375) SDCM 3 |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | (0.383, 0.377) SDCM 3 |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | (0.312, 0.327) SDCM 3 |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | (0.312, 0.325) SDCM 3 |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | (0.432, 0.400) SDCM 3 |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | (0.435, 0.401) SDCM 3 |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | (0.380, 0.375) SDCM 3 |

| Order Code | Full Product Name | Initial chromaticity |
|--------------|--|-----------------------|
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | (0.383, 0.377) SDCM 3 |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | (0.380, 0.375) SDCM 3 |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | (0.383, 0.377) SDCM 3 |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | (0.380, 0.375) SDCM 3 |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | (0.383, 0.377) SDCM 3 |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | (0.380, 0.375) SDCM 3 |
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | (0.383, 0.377) SDCM 3 |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | (0.383, 0.377) SDCM 3 |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | (0.383, 0.377) SDCM 3 |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | (0.380, 0.375) SDCM 3 |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | (0.383, 0.377) SDCM 3 |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | (0.380, 0.375) SDCM 3 |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | (0.383, 0.377) SDCM 3 |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | (0.380, 0.375) SDCM 3 |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | (0.383, 0.377) SDCM 3 |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | (0.380, 0.375) SDCM 3 |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | (0.383, 0.377) SDCM 3 |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | (0.312, 0.327) SDCM 3 |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | (0.312, 0.325) SDCM 3 |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | (0.432, 0.400) SDCM 3 |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | (0.435, 0.401) SDCM 3 |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | (0.380, 0.375) SDCM 3 |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | (0.380, 0.375) SDCM 3 |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | (0.383, 0.377) SDCM 3 |

Product Data


| Order Code | Full Product Name | Product family code |
|--------------|---------------------------------------|---------------------|
| 910505102953 | BY581P 700S/840 DIA WB GC SI | BY581P |
| 910505102954 | BY581P 700S/840 DIA HE WB GC SI | BY581P |
| 910505102955 | BY581P 700S/840 DIA WB GC SI BR | BY581P |
| 910505102956 | BY581P 700S/840 DIA HE WB GC SI BR | BY581P |
| 910505102865 | BY581X 250S/840 SIA WB GC SI H4 BR | BY580X |
| 910505102866 | BY581X 250S/840 SIA HE WB GC SI H4 BR | BY581X |
| 910505102856 | BY580X 130S/840 SIA WB GC SI H4 | BY580X |
| 910505102857 | BY580X 170S/840 SIA WB GC SI H4 | BY580X |
| 910505102858 | BY581X 250S/840 SIA WB GC SI H4 | BY580X |
| 910505102859 | BY581X 350S/840 SIA WB GC SI H4 | BY581X |

| Order Code | Full Product Name | Product family code |
|--------------|---|---------------------|
| 910505102860 | BY580X 130S/840 SIA HE WB GC SI H4 | BY580X |
| 910505102861 | BY580X 170S/840 SIA HE WB GC SI H4 | BY580X |
| 910505102862 | BY581X 250S/840 SIA HE WB GC SI H4 | BY581X |
| 910505102863 | BY581X 350S/840 SIA HE WB GC SI H4 | BY581X |
| 910505102868 | BY581X 250S/840 SIA WB GC SI ELP3 H4 | BY581X |
| 910505102869 | BY581X 250S/840 SIA WB GC SI ELW3 H4 | BY581X |
| 910505102870 | BY581X 250S/840 SIA HE WB GC SI ELP3 H4 | BY581X |
| 910505102871 | BY581X 250S/840 SIA HE WB GC SI ELW3 H4 | BY581X |
| 910505102864 | BY580X 170S/840 SIA WB GC SI H4 BR | BY580X |
| 910505102867 | BY580X 170S/840 SIA HE WB GC SI H4 BR | BY580X |


| Order Code | Full Product Name | Product family code |
|--------------|--|---------------------|
| 910505102872 | BY580P 170S/840 PSU WB GC SI | BY580P |
| 910505102874 | BY580P 170S/840 PSU HE WB GC SI | BY580P |
| 910505102878 | BY580P 130S/840 DIA WB GC SI | BY580P |
| 910505102879 | BY580P 170S/840 DIA WB GC SI | BY580P |
| 910505102882 | BY580P 130S/840 DIA HE WB GC SI | BY580P |
| 910505102883 | BY580P 170S/840 DIA HE WB GC SI | BY580P |
| 910505102886 | BY580P 170S/840 DIA WB PC SI | BY580P |
| 910505102890 | BY580P 170S/840 DIA HE WB PC SI | BY580P |
| 910505102894 | BY580P 170S/840 DIA WB GC SI ELP3 | BY580P |
| 910505102896 | BY580P 170S/840 DIA HE WB GC SI ELP3 | BY580P |
| 910505102898 | BY580P 130S/840 DIA MB GC SI | BY580P |
| 910505102899 | BY580P 170S/840 DIA MB GC SI | BY580P |
| 910505102903 | BY580P 130S/840 DIA HE MB GC SI | BY580P |
| 910505102904 | BY580P 170S/840 DIA HE MB GC SI | BY580P |
| 910505102914 | BY580P 170S/840 DIA NB GC SI | BY580P |
| 910505102916 | BY580P 170S/840 DIA HE NB GC SI | BY580P |
| 910505102918 | BY580P 170S/840 DIA XNB GC SI | BY580P |
| 910505102920 | BY580P 170S/840 DIA HE XNB GC SI | BY580P |
| 910505102922 | BY580P 170S/840 DIA HRO GC SI | BY580P |
| 910505102924 | BY580P 170S/840 DIA HE HRO GC SI | BY580P |
| 910505102926 | BY580P 170S/865 DIA WB GC SI | BY580P |
| 910505102928 | BY580P 170S/865 DIA HE WB GC SI | BY580P |
| 910505102930 | BY580P 170S/830 DIA WB GC SI | BY580P |
| 910505102932 | BY580P 170S/830 DIA HE WB GC SI | BY580P |
| 910505102934 | BY580P 170S/940 DIA WB GC SI | BY580P |
| 910505104548 | BY580P 170S/840 DIA WB GC SI MSP BR | BY580P |
| 910505104550 | BY580P 170S/840 DIA HE WB GC SI MSP BR | BY580P |
| 910505102888 | BY580P 170S/840 DIA WB GC SI BR | BY580P |
| 910505102892 | BY580P 170S/840 DIA HE WB GC SI BR | BY580P |
| 910505104544 | BY580P 170S/840 DIA WB GC SI SWP BR | BY580P |
| 910505104546 | BY580P 170S/840 DIA HE WB GC SI SWP BR | BY580P |
| 910505102889 | BY581P 250S/840 DIA WB GC SI BR | BY581P |

| Order Code | Full Product Name | Product family code |
|--------------|--|---------------------|
| 910505102893 | BY581P 250S/840 DIA HE WB GC SI BR | BY581P |
| 910505104545 | BY581P 250S/840 DIA WB GC SI SWP BR | BY581P |
| 910505104547 | BY581P 250S/840 DIA HE WB GC SI SWP BR | BY581P |
| 910505102873 | BY581P 250S/840 PSU WB GC SI | BY581P |
| 910505102875 | BY581P 250S/840 PSU HE WB GC SI | BY581P |
| 910505102877 | BY581P 200S/840 DIA UE WB GC SI | BY581P |
| 910505102880 | BY581P 250S/840 DIA WB GC SI | BY581P |
| 910505102881 | BY581P 350S/840 DIA WB GC SI | BY581P |
| 910505102884 | BY581P 250S/840 DIA HE WB GC SI | BY581P |
| 910505102885 | BY581P 350S/840 DIA HE WB GC SI | BY581P |
| 910505102887 | BY581P 250S/840 DIA WB PC SI | BY581P |
| 910505102891 | BY581P 250S/840 DIA HE WB PC SI | BY581P |
| 910505102895 | BY581P 250S/840 DIA WB GC SI ELD3 | BY581P |
| 910505102897 | BY581P 250S/840 DIA HE WB GC SI ELD3 | BY581P |
| 910505102901 | BY581P 250S/840 DIA MB GC SI | BY581P |
| 910505102902 | BY581P 350S/840 DIA MB GC SI | BY581P |
| 910505102905 | BY581P 250S/840 DIA HE MB GC SI | BY581P |
| 910505102906 | BY581P 350S/840 DIA HE MB GC SI | BY581P |
| 910505102915 | BY581P 250S/840 DIA NB GC SI | BY581P |
| 910505102917 | BY581P 250S/840 DIA HE NB GC SI | BY581P |
| 910505102919 | BY581P 250S/840 DIA XNB GC SI | BY581P |
| 910505102921 | BY581P 250S/840 DIA HE XNB GC SI | BY581P |
| 910505102923 | BY581P 250S/840 DIA HRO GC SI | BY581P |
| 910505102925 | BY581P 250S/840 DIA HE HRO GC SI | BY581P |
| 910505102927 | BY581P 250S/865 DIA WB GC SI | BY581P |
| 910505102929 | BY581P 250S/865 DIA HE WB GC SI | BY581P |
| 910505102931 | BY581P 250S/830 DIA WB GC SI | BY581P |
| 910505102933 | BY581P 250S/830 DIA HE WB GC SI | BY581P |
| 910505102935 | BY581P 250S/940 DIA WB GC SI | BY581P |
| 910505104549 | BY581P 250S/840 DIA WB GC SI MSP BR | BY581P |
| 910505104551 | BY581P 250S/840 DIA HE WB GC SI MSP BR | BY581P |


Polar Wide Diagrams



Polar Normal (separate) - BY580PI - 910505102872




Polar Normal (separate) - BY580PI - 910505102863




Polar Normal (separate) - BY580PI - 910505102914


Polar Wide Diagrams




Polar Normal (separate) - BY580PI - 910505102899




Polar Normal (separate) - BY580PI - 910505102869




Polar Normal (separate) - BY580PI - 910505102915




Polar Normal (separate) - BY580PI - 910505102865




Polar Normal (separate) - BY580PI - 910505102895




Polar Normal (separate) - BY580PI - 910505102898



Polar Normal (separate) - BY580PI - 910505102856




Polar Normal (separate) - BY580PI - 910505102924




Polar Normal (separate) - BY580PI - 910505102881


Polar Wide Diagrams




Polar Normal (separate) - BY580PI - 910505102925




Polar Normal (separate) - BY580PI - 910505102857




Polar Normal (separate) - BY580PI - 910505102933




Polar Normal (separate) - BY580PI - 910505102873




Polar Normal (separate) - BY580PI - 910505102902




Polar Normal (separate) - BY580PI - 910505102884



Polar Normal (separate) - BY580PI - 910505102874




Polar Normal (separate) - BY580PI - 910505102896




Polar Normal (separate) - BY580PI - 910505102875


Polar Wide Diagrams




Polar Normal (separate) - BY580PI - 910505102868




Polar Normal (separate) - BY580PI - 910505102923




Polar Normal (separate) - BY580PI - 910505102858




Polar Normal (separate) - BY580PI - 910505102871




Polar Normal (separate) - BY580PI - 910505102901




Polar Normal (separate) - BY580PI - 910505102922



Polar Normal (separate) - BY580PI - 910505102862




Polar Normal (separate) - BY580PI - 910505102906




Polar Normal (separate) - BY580PI - 910505102921


Polar Wide Diagrams




Polar Normal (separate) - BY580PI -
910505102920




Polar Normal (separate) - BY580PI -
910505102932




Polar Normal (separate) - BY580PI -
910505102864




Polar Normal (separate) - BY580PI -
910505102934




Polar Normal (separate) - BY580PI -
910505102878




Polar Normal (separate) - BY580PI -
910505102866



Polar Normal (separate) - BY580PI -
910505102885




Polar Normal (separate) - BY580PI -
910505102883




Polar Normal (separate) - BY580PI -
910505102918


Polar Wide Diagrams




Polar Normal (separate) - BY580PI - 910505102882




Polar Normal (separate) - BY580PI - 910505102916




Polar Normal (separate) - BY580PI - 910505102926




Polar Normal (separate) - BY580PI - 910505102928




Polar Normal (separate) - BY580PI - 910505102935




Polar Normal (separate) - BY580PI - 910505102903



Polar Normal (separate) - BY580PI - 910505102891




Polar Normal (separate) - BY580PI - 910505102904




Polar Normal (separate) - BY580PI - 910505102886


Polar Wide Diagrams




Polar Normal (separate) - BY580PI -
910505102867




Polar Normal (separate) - BY580PI -
910505102905




Polar Normal (separate) - BY580PI -
910505102890




Polar Normal (separate) - BY580PI -
910505102894




Polar Normal (separate) - BY580PI -
910505102930




Polar Normal (separate) - BY580PI -
910505102919



Polar Normal (separate) - BY580PI -
910505102879




Polar Normal (separate) - BY580PI -
910505102870




Polar Normal (separate) - BY580PI -
910505102887


Polar Wide Diagrams




Polar Normal (separate) - BY580PI -
910505102859




Polar Normal (separate) - BY580PI -
910505102892




Polar Normal (separate) - BY580PI -
910505102893




Polar Normal (separate) - BY580PI -
910505102860




Polar Normal (separate) - BY580PI -
910505102929




Polar Normal (separate) - BY580PI -
910505102931



Polar Normal (separate) - BY580PI -
910505102917




Polar Normal (separate) - BY580PI -
910505102877




Polar Normal (separate) - BY580PI -
910505102889


Polar Wide Diagrams




Polar Normal (separate) - BY580PI - 910505102927




Polar Normal (separate) - BY580PI - 910505102861




Polar Normal (separate) - BY580PI - 910505102888




Polar Normal (separate) - BY580PI - 910505102880




Polar Normal (separate) - BY580PI - 910505102897




Polar Normal (separate) - BY580PI - 910505104548



Polar Normal (separate) - BY580PI - 910505104547




Polar Normal (separate) - BY580PI - 910505104550




Polar Normal (separate) - BY580PI - 910505104549


Polar Wide Diagrams




Polar Normal (separate) - BY580PI -
910505104545



Polar Normal (separate) - BY580PI -
910505104544



Polar Normal (separate) - BY580PI -
910505104551



Polar Normal (separate) - BY580PI -
910505104546

