



For top performance and sustainability

MASTER LEDtube T8 UltraEfficient

With energy prices rising and the EU's Green Deal² continuing to fund energy efficient building renovations, many are looking into make their company's lighting more sustainable. The new Philips MASTER LEDtube Ultra Efficient T8 is a true breakthrough on the way to more sustainable lighting. It replaces your current fluorescent tube or LED tube directly and offers immediately great energy cost reduction as well as a much longer lifetime!

Benefits

- Absolute performance in energy saving: up to 44% compared with standard LED tube
- Reliable performance of up to 100,000 hours
- Energy cost and CO₂ savings from the start

Features

- Ultra efficiency achieve an incredible class A/B energy efficiency rating
- Up to 100,000 hours lifetime
- Plastic design makes it true shatterproof according to IEC 61549 standards
- Rotatable end-cap that gives light where needed
- HACCP-enabled, supported by product level NSF certificate

Application

- Industry & warehouse
- Office, education & retail


MASTER LEDtube T8 UltraEfficient

Versions



LEDtube 1200mm 15W G13

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm UE 20W 865 T8	25.8 mm	28 mm	1,498.8 mm	1,505.9 mm	1,513 mm

