



Luma gen2 Solar – Using Solar power to light up your streets

Luma gen2 Solar

Meet your sustainability targets in an easy and fast way. we upgraded your most preferred luminaire Luma gen2 to be powered by Solar energy. Finless design, future-proof architecture, hustle-free maintenance and best in class lighting performance are some of the reasons we are proud of Luma gen2 Solar. Let's take a deep dive in all the characteristics we worked on to meet your lighting needs.

Benefits

- Compatible with a wide range of PHILIPS Solar sub-systems which include Battery, PV Panel, Charge Controller for both OFF-Grid and HY-Brid power options
- Customizable lighting solutions to suit your exact needs thanks to Ledgine – O.
- Best in class efficiency and light performance in a broad range of applications
- Dedicated light recipes for:
 - oDecreased light pollution
 - oOptimal ecosystem for bats
 - oPreservation of a dark night sky
- Improved serviceability thanks to Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information
- Redesigned cable feed-through for tool-less access to the connection compartment

Luma gen2 Solar

Features

- Dedicated Philips Solar sub-systems like Charge Controller, Battery, PV panel, connecting cables with IP67 connectors enabling faster, safer, installation and maintenance
- New cable feedthrough for easy installation
- Tilt now with 2,5 degrees precision
- Choice of 40+ different beams and option of different internal louvers
- Efficacy up to 165 lm/W

Application

- Roads and streets
- Residential streets

Versions



Luma gen2 medium Solar

Dimensional drawing

Luma gen2 Solar

Product details



Luma gen2 mini Solar bottom view



Luma gen2 mini Solar side view



Luma gen2 medium Solar Spigot



Luma gen2 medium Solar Spigot



Luma gen2 medium Solar top view



Luma gen2 mini Solar top view



Luma gen2 medium Solar with louver

Luma gen2 medium Solar side view



Luma gen2 Solar

Product details



Luma gen2 medium Solar

General Information

Driver included	No
Light source replaceable	Yes

Light Technical

Luminaire light beam spread	155° x 86°
Optical cover type	Glass
Optic type outdoor	Distribution medium 10
Standard tilt angle side entry	0°
Standard tilt angle posttop	-
Upward light output ratio	0

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	Dark gray
---------------	-----------

Approval and Application

CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Mech. impact protection code	IK10
Ingress protection code	IP66
Surge Protection (Common/Differential)	-

General Information

Order Code	Full Product Name	Product family code
910925868310	VGP703 40 4S 730 24V III DM10 42/60S	VGP703
910925868311	VGP703 40 4S 830 24V III DM10 42/60S	VGP703
910925868312	VGP703 40 4S 740 24V III DM10 42/60S	VGP703
910925868313	VGP704 80 4S 730 48V III DM10 42/60S	VGP704
910925868314	VGP704 80 4S 830 48V III DM10 42/60S	VGP704
910925868315	VGP704 80 4S 740 48V III DM10 42/60S	VGP704

Light Technical

Order Code	Full Product Name	Light source color	Correlated		
			Color Temperature (Nom)	Color rendering index (CRI)	Number of light sources
910925868310	VGP703 40 4S 730 24V III DM10 42/60S	warm white	3000 K	>70	1

Order Code	Full Product Name	Light source color	Correlated		
			Color Temperature (Nom)	Color rendering index (CRI)	Number of light sources
910925868311	VGP703 40 4S 830 24V III DM10 42/60S	warm white	3000 K	>80	1

Luma gen2 Solar

Order Code	Full Product Name	Light source color	Correlated		
			Color Temperature (Nom)	Color rendering index (CRI)	Number of light sources
910925868312	VGP703 40 4S	740	4000 K	>70	1
	740 24V III DM10	neutral			
	42/60S	white			
910925868313	VGP704 80 4S	730 warm	3000 K	>70	2
	730 48V III DM10	white			
	42/60S				

Order Code	Full Product Name	Light source color	Correlated		
			Color Temperature (Nom)	Color rendering index (CRI)	Number of light sources
910925868314	VGP704 80 4S	830 warm	3000 K	>80	2
	830 48V III DM10	white			
	42/60S				
910925868315	VGP704 80 4S	740	4000 K	>70	2
	740 48V III DM10	neutral			
	42/60S	white			

