

# Product Description

## TUV PL-L

TUV PL-L lamps are compact UVC (germicidal) lamps used in residential water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

### Benefits

- Security of effective disinfection over the useful lifetime of the lamp
- Security of effective disinfection over the complete lifetime of the lamp
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection

## Features

- Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection purposes
- Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection purposes
- Protective inside coating ensures constant UV output over the complete lifetime of the lamp
- Protective inside coating ensures constant UV output over the complete lifetime of the lamp
- Special lamp glass filters out the 185 nm ozone-forming radiation
- Special lamp glass filters out the 185 nm ozone-forming radiation
- High Output versions contain wind-chill correction for improved performance in moving air and reducing amount of required lamps
- High Output versions contain wind-chill correction for improved performance in moving air and reducing amount of required lamps
- High Output versions for optimum UVC output per lamp length, allowing for reduction of system size
- High Output versions for optimum UVC output per lamp length, allowing for reduction of system size
- Warning sign on lamp indicates that the lamp radiates UVC
- Warning sign on lamp indicates that the lamp radiates UVC


## Application

- Deactivation of bacteria, viruses and other micro-organisms
- Deactivation of bacteria, viruses and other micro-organisms
- Residential drinking water units
- Residential drinking water units
- Fish pond and process water units
- Fish pond and process water units
- In-duct air treatment units
- In-duct air treatment units
- Stand alone air purifiers
- Stand alone air purifiers
- Air disinfection systems in for example hospitals, universities and laboratories
- Air disinfection systems in for example hospitals, universities and laboratories

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 18W/4P 1CT/25	18 mm	39 mm	195 mm	220 mm	225 mm
TUV PL-L 24W/4P UNP/50	18 mm	39 mm	290 mm	315 mm	320 mm
TUV PL-L 36W/4P 1CT/25	18 mm	38 mm	385 mm	410 mm	415 mm
TUV PL-L 55W/4P HF 1CT/25	18 mm	38 mm	505 mm	530 mm	535 mm
TUV PL-L 95W/4P HO 1CT/25	18 mm	38 mm	505 mm	530 mm	535 mm

### General Information

Cap-Base 2G11

### Light Technical

Color Designation -

### Approval and Application

Mercury (Hg) Content (Nom) 4.4 mg

## Light Technical

Order Code	Full Product Name	Color Code
927903004007	TUV PL-L 18W/4P 1CT/25	-
927903204016	TUV PL-L 24W/4P UNP/50	TUV
927903404007	TUV PL-L 36W/4P 1CT/25	-

Order Code	Full Product Name	Color Code
927908704007	TUV PL-L 55W/4P HF 1CT/25	-
927909804007	TUV PL-L 95W/4P HO 1CT/25	-

## Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927903004007	TUV PL-L 18W/4P 1CT/25	0.375 A	18 W
927903204016	TUV PL-L 24W/4P UNP/50	0.345 A	24 W
927903404007	TUV PL-L 36W/4P 1CT/25	0.435 A	36 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927908704007	TUV PL-L 55W/4P HF 1CT/25	0.525 A	55 W
927909804007	TUV PL-L 95W/4P HO 1CT/25	0.8 A	90 W

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
927903004007	TUV PL-L 18W/4P 1CT/25	-
927903204016	TUV PL-L 24W/4P UNP/50	2xT16
927903404007	TUV PL-L 36W/4P 1CT/25	-

Order Code	Full Product Name	Bulb Shape
927908704007	TUV PL-L 55W/4P HF 1CT/25	-
927909804007	TUV PL-L 95W/4P HO 1CT/25	-

