

PHILIPS

Bulb 120W A67 E27

LED

3000K

1650lm

10000h



8718699640477



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Contains no mercury

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Frosted
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions

- Height: 13.2 cm
- Width: 6.8 cm

Design and finishing

- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)
- Ambient temperature range: -20 to +45 °C

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 1650 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 830 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 1,650 lm
- Luminous Efficacy (rated) (Nom): 113 lm/W

Miscellaneous

- EyeComfort: No

Other characteristics

- Efficacy: 113 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699640477
- EOC: 871869964047700
- Product title: LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR

Power

- Power Factor (Fraction): 0.51

Power consumption

- Power factor: 0.51
- Voltage: 220-240 V
- Wattage: 14.5 W
- Wattage equivalent: 120 W
- Power Consumption: 14.5 W

Product dimensions and weight

- Length: 13.2 cm

Rated values

- Rated lifetime: 12,000 hour(s)

Technical specifications

- Frequency: 50-60 Hz
- Dimmable: No
- Cap-Base: E27

Packaging dimensions and weight

- EAN/UPC - product: 8718699640477
- Net weight: 0.13 kg
- Gross weight: 0.17 kg
- Height: 13.8 cm
- Length: 6.9 cm
- Width: 6.9 cm



Issue date: 2024-11-21
Version: 0.95

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com