

PHILIPS

Capsule 40W G9
G9

LED

2700K

480lm

15000h

Dimming



8720169301573



Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- True incandescent-like warm white light

Choose for a sustainable solution

- Saves up to 80% Energy

Create the right light for your home

- A simple LED for everyday use

Highlights

Incandescent-like warm white



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for

relaxing. This 2700K light is ideal for home lighting design

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: G9
- Dimmable: Only with specific dimmers
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions

- Height: 5.9 cm
- Width: 1.8 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 320 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 480 lm

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 120 lm/W

Packaging information

- EAN: 8720169301573
- EOC: 872016930157300
- Product title: LED 40W G9 WW 230V Dim SRT6

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage: 4 W
- Wattage equivalent: 40 W
- Energy Efficiency Label (EEL): E

Product dimensions and weight

- Length: 5.9 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1932585

Packaging dimensions and weight

- EAN/UPC - product: 8720169301573
- Net weight: 0.01 kg
- Gross weight: 0.01 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm
- Material number (12NC):
929003791248



Issue date: 2024-07-25
Version: 0.228

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com