

**FEATURES**

- Heavy-duty, 20-gauge steel housing with canopy
- Dual voltage input 120/277 VAC, 60Hz
- White, powder-coat finish
- Long-life, energy-efficient LEDs
- Sealed nickel cadmium batteries with 15-year life expectancy
- Universal, field-selectable chevrons
- Ceiling, wall and end mounting

**ENERGY DATA**

See Specification Sheet for Energy Data

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

**COMPLIANCES:** UL924 Listed; Damp Location, NYC Code Compliant




**RXS - STEEL EXIT SIGNS**

**ORDERING INFORMATION**

**SAMPLE NUMBER:** RXSN8RU

| Family               | Battery                     | Letter Size | Letter Color | Number of Faces                |
|----------------------|-----------------------------|-------------|--------------|--------------------------------|
| RXS=Rival Steel Exit | A=AC-Only<br>N=Self-Powered | 8=8"        | R=Red        | U=Universal (One or Two Faces) |

**CEILING MOUNT**



**END MOUNT**

